

# Product data sheet

Specifications



Extended rotary handle kit, TeSys  
Deca frame 3, IP65, red  
handle, without trip indication, for  
GV3L/GV3P

GV3APN04

## Main

Range	TeSys
Device short name	GV3AP
Product or component type	Rotary handle kit
Accessory / separate part category	Control accessory
Handle colour	Red
Handle front plate colour	Yellow

## Complementary

Product compatibility	GV3P GV3L
Rotary handle padlocking	Padlock in OFF position
Rotary handle mounting style	Extended
Locking options description	1 to 3 padlocks
Back/door distance	189...300 mm
Product weight	0.3 kg

## Environment

Product certifications	CULus
IP degree of protection	IP65

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.800 cm
Package 1 Width	9.100 cm
Package 1 Length	37.200 cm
Package 1 Weight	360.000 g

## Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Total lifecycle Carbon footprint **30**

Environmental Disclosure [Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **No**

[EU RoHS Directive](#) **Compliant with Exemptions**

SCIP Number **2057c252-f956-4ac1-a3d9-75119bc8a000**

REACH Regulation [REACH Declaration](#)

California proposition 65  
WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to [www.P65Warnings.ca.gov](#)

## Use Again


### Repack and remanufacture

End of life manual availability [End of Life Information](#)


Take-back **No**

WEEE Label The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins


## Dimensions Drawings

Mounting**Mounting of External Operator GV3APN01, GV3APN02 or GV3APN04 for Motor Circuit Breakers GV3L**

Door cut-out




(1) For IP65 only.

**Mounting of External Operator GVAPH03 for Motor Circuit Breakers GV3L**

	b	
	Minimum	Maximum
GV3APN <sub>**</sub> + GVAPH03	200	300
GV3APN <sub>**</sub> + GVAPH03 + GVAPK12	300	492

Door cut-out



(1) For IP65 only.

Image of product / Alternate images

Alternative

---



