

Product data sheet

Characteristics

AK5PC34

Plug outlet, Linergy HK, 3P+N, 32A, 2 points, 4 mm², cable length 250mm



Main

Range	Linergy
Product name	HK
Product or Component Type	Plug outlet
Poles description	3P + N
[I _{th}] conventional free air thermal current	32 A
I ² t on activation	200000 A ² .s
Number of points	2
Number of cables	4 0.01 in ² (4 mm ²)
Cable length	0.82 ft (0.25 m)
Quantity per Set	Set of 6

Complementary

[Ui] rated insulation voltage	600 V CSA 600 V UL 690 V IEC 60439-1
Peak current	25 kA
Width	1.42 in (36 mm)
Height	1.81 in (46 mm)
Depth	1.50 in (38 mm)
Net Weight	0.11 lb(US) (0.05 kg)

Environment

Standards	IEC 60439
Product Certifications	UL LROS (Lloyds register of shipping) CSA DNV

Ordering and shipping details

Category	22623-PANEL BUS (AK5)
Discount Schedule	I11
GTIN	3389110576870
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.31 in (13.500 cm)
Package 1 Width	5.00 in (12.700 cm)
Package 1 Length	6.10 in (15.500 cm)
Package 1 Weight	2.47 oz (70.000 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	5.31 in (13.500 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Package 2 Width	5.00 in (12.700 cm)
Package 2 Length	6.10 in (15.500 cm)
Package 2 Weight	17.43 oz (494.000 g)
Unit Type of Package 3	S04
Number of Units in Package 3	96
Package 3 Height	11.81 in (30.000 cm)
Package 3 Width	15.75 in (40.000 cm)
Package 3 Length	23.62 in (60.000 cm)
Package 3 Weight	19.14 lb(US) (8.681 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------