

Product data sheet

Specifications

SQUARE D



Foot Switch, Harmony 9002AW, industrial, oversized pedal and side shields, SPDT contact, NEMA 4, 13, two stage, 5A at 600V AC

9002AW134

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range	9002AW
Product	Foot switch
Contact Operation	2 steps
Certifications	CSA UL Listed
Cable Entry	0.75 inch NPT conduit entrance
Contact Arrangement	SPDT per step
Enclosure Rating	NEMA 2/4/13
Voltage Rating	600 V AC/DC
Protection	Oversized pedal shield Side shield
Operator Action	Spring return
Rated Breaking Capacity	15 A 120 V AC inductive control circuit UL 508 10 A 240 V AC inductive control circuit UL 508 6 A 480 V AC inductive control circuit UL 508 5 A 600 V AC inductive control circuit UL 508 15 A 120 V AC resistive control circuit UL 508 0.5 A 125 V DC resistive control circuit UL 508
Height	6.3 in (159 mm)
Width	6.4 in (163 mm)
Depth	8.5 in (217 mm)

Ordering and shipping details

Category	US10CS121441
Discount Schedule	0CS1
GTIN	785901044789
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	15.24 in (38.71 cm)
Package 1 Width	6.00 in (15.24 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	38.71 in (98.322 cm)
Package weight(Lbs)	10.659 lb(US) (4.835 kg)

Contractual warranty

Warranty	18 months
----------	-----------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle)

36

Use Better

Materials and Substances

Packaging made with recycled cardboard

Yes

Packaging without single use plastic

Yes

[EU RoHS Directive](#)

Pro-active compliance (Product out of EU RoHS legal scope)

California proposition 65

WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture

Circularity Profile

No need of specific recycling operations

Take-back

No

Image of product / Alternate images

Alternative



