

# Product data sheet

## Characteristics

# TCSEGW B13FA0

## universal automation Wifi Interface - IP20 - with RJ45 and USB connectors

Product availability: Stock - Normally stocked in distribution facility



### Main

Accessory / separate part category	Communication accessory
Accessory / separate part type	Wireless access point
Accessory / separate part destination	PC PLC Variable speed drive Smart phone Tablet Phablet

### Complementary

Range compatibility	Modicon M251 Modicon M580 Altvivar Process ATV600 Altvivar Process ATV900
Kit composition	USB cable Battery Quick start guide Power adaptor Ethernet cable
Function available	Automatic detection of Schneider-Electric products and other devices on Ethernet
Connector type	Female RJ45 automatic negotiation of 10/100 Mbit/s Micro USB type A female
Communication port protocol	DHCP Ethernet TCP/IP ICMP PPPoE (Point-to-Point Protocol over Ethernet)
Method of access	CSMA/CA CSMA/CD
Operating system	Windows Vista Windows XP Windows 7 Windows 8 Android Mac iOS
System requirements	Microsoft internet explorer Apple Safari Firefox Google Chrome
Supply	Rechargeable internal battery
Local signalling	1 LED green, orange and red battery status 1 LED Ethernet port activity 1 LED wireless function status 1 LED scan status
Product weight	0.77 lb(US) (0.35 kg)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

IP degree of protection	IP20
Ambient air temperature for operation	32...104 °F (0...40 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Relative humidity	10...90 % for operation, without condensation conforming to IEC 60068-2-3 5...90 % for storage, without condensation conforming to IEC 60068-2-3
Standards	IEEE 802.3 IEEE 802.3u IEEE 802.3x IEEE 802.11b IEEE 802.11g IEEE 802.11n IEEE 802.1x
Product certifications	CE FCC

## Ordering and shipping details

Category	22205 - ATV630 FRAMES 1 & 2
Discount Schedule	CP4E
GTIN	00785901691730
Nbr. of units in pkg.	1
Package weight(Lbs)	0.7700000000000002
Returnability	Y
Country of origin	CN


## Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1451 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

---

Presentation

---



Item	Description
(1)	Power switch
(2)	Micro USB port
(3)	Reset button
(4)	Ethernet port