

# Product data sheet

Specifications

SQUARE D



Foot Switch, Harmony, industrial, unshielded, maintained contact, 3A at 230 VAC, SPST contact, NEMA 2, 4, 13 enclosure

9002AW11

**Product availability:** Non-Stock - Not normally stocked in distribution facility

## Main

Range	9002AW
Product	Foot switch
Contact Operation	1 step
Certifications	CSA UL Listed
Cable Entry	0.75 inch NPT conduit entrance
Contact Arrangement	SPST
Enclosure Rating	NEMA 2/4/13
Voltage Rating	600 V AC/DC
Protection	Unshielded
Operator Action	Maintained
Rated Breaking Capacity	6 A 115 V AC inductive control circuit UL 508 3 A 230 V AC inductive control circuit UL 508 2.2 A 125 V DC inductive control circuit UL 508 2.2 A 125 V DC resistive control circuit UL 508 1.1 A 250 V DC inductive control circuit UL 508 1.1 A 250 V DC resistive control circuit UL 508
Height	3.9 in (99 mm)
Width	4.5 in (114 mm)
Depth	8.5 in (216 mm)

## Ordering and shipping details

Category	US10CS121441
Discount Schedule	0CS1
GTIN	785901816737
Returnability	Yes
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	3.30 in (8.382 cm)
Package 1 Width	4.90 in (12.446 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

---

Package 1 Length	9.10 in (23.114 cm)
Package weight(Lbs)	3.100 lb(US) (1.406 kg)

---

## Contractual warranty

---

Warranty	18 months
----------	-----------



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle)

10

## Use Better

### Materials and Substances

Packaging made with recycled cardboard

Yes

Packaging without single use plastic

Yes

[EU RoHS Directive](#)

Pro-active compliance (Product out of EU RoHS legal scope)

California proposition 65

**WARNING:** This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

## Use Again

### Repack and remanufacture

Circularity Profile

No need of specific recycling operations

Take-back

No

WEEE Label

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative

---



