

# Product data sheet

Specifications



Legend holder 30x50mm, Harmony XB4, plastic, with legend 18x27mm, unmarked

ZBY6101

Product availability: Stock - Normally stocked in distribution facility

## Main

Product or Component Type	Legend holder
Accessory / separate part category	Marking accessory

## Complementary

Material	Plastic
Device Composition	Blank legend Legend holder
Accessory / separate part destination	Ø 22 mm control or signalling unit with square head Ø 22 mm control or signalling unit with circular head For standard head
Colour	Dark grey
Range Compatibility	Harmony XB4 Harmony XB5
Legend holder size	30 x 50 mm
Marking	unmarked 1 black side, 1 red side
Sale per indivisible quantity	10
Product Weight	0.004 lb(US) (0.002 kg)

## Ordering and shipping details

Category	US10CS222469
Discount Schedule	0CS2
GTIN	3389110095869
Returnability	Yes
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	0.16 in (0.400 cm)
Package 1 Width	1.18 in (3.000 cm)
Package 1 Length	1.97 in (5.000 cm)
Package weight(Lbs)	0.039 oz (1.100 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 2 Height	0.59 in (1.500 cm)
Package 2 Width	3.15 in (8.000 cm)
Package 2 Length	4.33 in (11.000 cm)
Package 2 Weight	0.670 oz (19.000 g)
Unit Type of Package 3	S01
Number of Units in Package 3	400
Package 3 Height	5.91 in (15.000 cm)
Package 3 Width	5.91 in (15.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	32.840 oz (931.000 g)

## Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
<a href="#">EU RoHS Directive</a>	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	<a href="#">REACH Declaration</a>
California proposition 65	<b>WARNING:</b> This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

## Use Again

### Repack and remanufacture

Take-back	No
-----------	----

## Offer Marketing Illustration

## Product benefits / Features

## Technical Benefits

## Harmony XB4

Conformity with IEC, UL, CSA, CCC EAC, and JIS standards, as well as CE marking and marine approvals

Up to IP66, 67, 69, 69K, and type 4X protection ratings

High vibration resistance with shake-proof terminal screws

Operating temperature from -40°C to 70°C

Shock protection level up to IK06

Secure switching of inductive or heavy DC loads directly – 100 000 operations at 10A, 24V dc

## Offer Marketing Illustration

## Product benefits / Features




Image of product / Alternate images

Alternative

---





