

Product data sheet

Specifications

SQUARE D



Mini circuit breaker, QOU, 20A, 2 pole, 120/240VAC, 10kA

QOU220

Product availability: Stock - Normally stocked in distribution facility

Main

Product or Component Type Miniature circuit-breaker

Range of Product QOU

Circuit breaker type Standard

Circuit breaker application HACR rated

Complementary

Line Rated Current 20 A

Electrical connection Slotted box lugs, line side
Slotted box lugs, load side

[Ue] rated operational voltage 120/240 V AC
120 V AC
48 V DC

Mounting Mode Unit mount

AWG gauge AWG 14...AWG 2 aluminium/copper

Height 4.05 in (102.87 mm)

Width 1.5 in (38.1 mm)

Depth 2.95 in (74.93 mm)

Tightening torque 45 lbf.in (5.08 N.m) (AWG 14...AWG 2)

Environment

Product Certifications CSA
IEC
UL Listed

Ordering and shipping details

Category US10DE200900

Discount Schedule 0DE2

GTIN 785901418689

Returnability Yes

Country of origin MX

Packing Units

Unit Type of Package 1 PCE

Nbr. of units in pkg. 1

Package 1 Height 2.00 in (5.080 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	3.70 in (9.398 cm)
Package 1 Length	4.90 in (12.446 cm)
Package weight(Lbs)	12.160 oz (344.730 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	24
Package 2 Height	3.80 in (9.652 cm)
Package 2 Width	13.80 in (35.052 cm)
Package 2 Length	20.50 in (52.070 cm)
Package 2 Weight	18.459 lb(US) (8.373 kg)

Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle)	19
--	-----------

Environmental Disclosure	Product Environmental Profile
--------------------------	---

Use Better

Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant
SCIP Number	Af42fb01-813d-40c0-ae28-b8b3299dbc99
REACH Regulation	REACH Declaration
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
Halogen content performance	Halogen free product

Use Again

Repack and remanufacture

Circularity Profile	No need of specific recycling operations
Take-back	No

Technical Illustration

Dimensions

