

# Product data sheet

Specifications



Disconnect switch, TeSys VLS, recessed rotary handle, screw mounting, 65x65mm, red handle, 5mm shaft

VLSH1S5R

**Product availability:** Stock - Normally stocked in distribution facility

## Main

Range	TeSys
Device short name	VLSH
Product or Component Type	Rotary handle
Range compatibility	TeSys TeSys VARIO LS VLS3P
Handle colour	Red
Handle front plate colour	Yellow
Rotary handle padlocking	1 to 3 padlocks 0.2...0.3 in (4...8 mm)
Marking	0 - 1 OFF-ON

## Complementary

Fixing mode	By 4 screws
Tightening torque	20.4 lbf.in (2.3 N.m)
Base dimension	65 x 65 mm
Height	2.6 in (65 mm)
Width	2.6 in (65 mm)
Depth	1.8 in (46 mm)
Net Weight	0.161 lb(US) (0.073 kg)

## Environment

IP Degree of Protection	IP65
NEMA degree of protection	NEMA 1 NEMA 4 NEMA 4X

## Ordering and shipping details

Category	US10CP121734
Discount Schedule	OCP1
GTIN	3606481156891
Returnability	Yes
Country of origin	IT

## Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

<b>Unit Type of Package 1</b>	PCE
<b>Nbr. of units in pkg.</b>	1
<b>Package 1 Height</b>	1.97 in (5.000 cm)
<b>Package 1 Width</b>	2.56 in (6.500 cm)
<b>Package 1 Length</b>	2.56 in (6.500 cm)
<b>Package weight(Lbs)</b>	2.293 oz (65.000 g)
<b>Unit Type of Package 2</b>	S02
<b>Number of Units in Package 2</b>	40
<b>Package 2 Height</b>	5.91 in (15.000 cm)
<b>Package 2 Width</b>	11.81 in (30.000 cm)
<b>Package 2 Length</b>	15.75 in (40.000 cm)
<b>Package 2 Weight</b>	6.288 lb(US) (2.852 kg)



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Use Better

#### Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
<a href="#">EU RoHS Directive</a>	Pro-active compliance (Product out of EU RoHS legal scope)

### Use Again

#### Repack and remanufacture

Circularity Profile	No need of specific recycling operations
Take-back	No