

Product data sheet

Specifications



Pump Panel, NEMA Type S, Well Guard, oil field, Size 1, 27A, 10HP, HLL36030M71 circuit breaker, Motor Logic SSOLR, 480VAC 60Hz coil, NEMA 3R

8940XC4S2V06H30

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product	Well-Guard Control
Type	S2
Device Application	Pumping

Complementary

Control Circuit Type	Common control circuit
Control Circuit Voltage	480 V AC 60 Hz 440 V AC 50 Hz
Line Rated Current	27 A
Number of Poles	3
Horsepower Rating	10 hp 480 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Selector switch HAND-OFF-AUTO)
Disconnect Type	Associated circuit breaker
Circuit breaker CT rating	30 A
Circuit breaker type	HLL
Thermal overload type	Motor Logic solid state class 10/20
Protection Type	Overload Phase loss Phase unbalance
Device mounting	Surface
Electrical Connection	Screw terminal
NEMA size	1
Height	38.5 in (978 mm)
Width	20.4 in (519 mm)
Depth	9.4 in (239 mm)

Environment

NEMA Rating	NEMA 3R
Enclosure type	Weatherproof enclosure indoor/outdoor

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Certifications	UL Listed NEMA
------------------------	-------------------

Ordering and shipping details

Category	US10CP121395
Discount Schedule	0CP1
GTIN	785901973393
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	12.99 in (33.0 cm)
Package 1 Width	21.50 in (54.6 cm)
Package 1 Length	40.98 in (104.1 cm)
Package weight(Lbs)	86.0002 lb(US) (39.009 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	Yes
EU RoHS Directive	Under investigation
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

 Repack and remanufacture	
Take-back	No