

Product data sheet

Specifications

APC



NetShelter SV 48U 600mm Wide x 1200mm Deep Enclosure with Sides Black

AR2507

Product availability: Non-Stock - Not normally stocked in distribution facility

Overview

Presentation	Deep and Tall Universal IT Enclosure for low to medium density server and networking applications that either require additional equipment clearance space or more open space for ease of access in the rear of the enclosure. Tall to provide 48U spaces for environments that can take advantage of higher spaces and provide more mounting u-spaces at each enclosure footprint. Compact width to optimize data center space.
---------------------	--

Lead time	Usually in Stock
------------------	------------------

Main

Product or Component Type	Rack enclosure
Number of rack unit	48U
Provided equipment	Baying hardware Doors Key(s) Keyed-alike doors and side panels Leveling feet Mounting Hardware Pre-installed casters 4 x Bolt down brackets Roof Side Panels Unpacking sheet

Physical

Height	91.50 in (232.4 cm)
Width	23.62 in (60 cm)
Depth	47.24 in (120 cm)
Product Weight	289.2 lb(US) (131.2 kg)
Color	Black
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	36.10 in (91.69 cm)
Minimum Mounting Depth	6.60 in (16.76 cm)
Rack Width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 18 gauge post 16 gauge rear door 19 gauge roof 18 gauge side panels
Permanent permissible load	1014 lb(US) (459.9 kg) dynamic 2205 lb(US) (1000.2 kg) static

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	731304302100
Returnability	No
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	96.38 in (244.8 cm)
Package 1 Width	27.56 in (70 cm)
Package 1 Length	51.18 in (130 cm)
Package weight(Lbs)	333.740 lb(US) (151.382 kg)

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle)	460
--	-----

Use Better

Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	REACH Declaration

Use Again

Repack and remanufacture

Circularity Profile	End of Life Information
Take-back	No

Image of product / Alternate images

Alternative















