

Product data sheet

Specifications



Fuse holder, Square D 9080FB, max 30A rated, 600VAC/DC, Class J type fuses, 3 pole, surface mount

9080FB3611J

Product availability: Stock - Normally stocked in distribution facility

Main

Range	9080FB
Product	Fuse holder

Complementary

Current Rating	30 A
[Ue] rated operational voltage	<= 600 V AC/DC
Fuse type	J
Fuse size	0.8125 x 2.25 in
Number of poles	3
Electrical Connection	Box lugs
Wire Gauge	AWG 14...AWG 2 copper or aluminium
SCCR	200 kA UL 512
Product Certifications	CSA file 70360 class 6225 01 CE UL listed file E40747 CCN IZLT
Operating Temperature	-40...125 °C (-40...257 °F)
Mounting Type	Surface mount
Block Material	Thermoplastic: block
Wire stripping length	0.4375 in (11.1125 mm)
Terminal Tightening Torque	screw terminals 25 lbf.in (2.8 N.m) AWG 14...AWG 6 copper
Height	4.07 in (103.38 mm)
Width	4.72 in (119.89 mm)
Depth	2.09 in (53.09 mm)

Ordering and shipping details

Category	US10CP121701
Discount Schedule	0CP1
GTIN	785901139638
Returnability	Yes
Country of origin	US

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	2.00 in (5.080 cm)
Package 1 Width	3.30 in (8.382 cm)
Package 1 Length	3.40 in (8.636 cm)
Package weight(Lbs)	5.600 oz (158.757 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	20
Package 2 Height	4.40 in (11.176 cm)
Package 2 Width	9.90 in (25.146 cm)
Package 2 Length	17.50 in (44.450 cm)
Package 2 Weight	8.009 lb(US) (3.633 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

 Repack and remanufacture	
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.