

# 70-BSMM-240

Protection module with MOV suppressor, SE  
Relays, for 782H hermetically sealed relays,  
240VAC/VDC



## Main

|                       |                                                |
|-----------------------|------------------------------------------------|
| Product Range         | Harmony Electromechanical Relays               |
| Product Type          | Protection module                              |
| Product Compatibility | Socket 70-781 plug-in<br>Socket 70-782 plug-in |
| Device Application    | Protection                                     |

## Complementary

|                                |                    |
|--------------------------------|--------------------|
| [Ue] rated operational voltage | 240 V              |
| Protection Technology          | MOV                |
| Width                          | 0.49 in (12.45 mm) |
| Depth                          | 0.34 in (8.64 mm)  |

## Ordering and shipping details

|      |               |
|------|---------------|
| GTIN | 3606480278358 |
|------|---------------|


## Offer Sustainability

|                            |                                                                                                                                                                                                                                                                                                                                                                        |
|----------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                                                                                                                                                                                                  |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                                                                                                                      |
| REACH free of SVHC         | Yes                                                                                                                                                                                                                                                                                                                                                                    |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                                                                                                         |
| Toxic heavy metal free     | Yes                                                                                                                                                                                                                                                                                                                                                                    |
| Mercury free               | Yes                                                                                                                                                                                                                                                                                                                                                                    |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                                                                                                                                    |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                                                                                                                                                                                                                                                                                                                                 |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                                                                                                                                          |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.                                                                                                                                                                                                                                           |

---

Wiring Diagram

---



- (1) : MOV Suppressor  
(2) : Protection Diode  
(3) : LED Indicator  
(4) : RC Suppressor