

Product data sheet

Specifications



Reduced Voltage Pump Panel Size 5, Motor Logic SSOLR, 480 VAC, NEMA 3R +Options

8940RG3QV06

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product	Well-Guard Control
Type	class 8940 type R
Device Application	Pumping

Complementary

Control Circuit Type	Common control circuit
Control Circuit Voltage	480 V AC 60 Hz 440 V AC 50 Hz
Line Rated Current	270 A
Number of Poles	3
Horsepower Rating	200 hp 480 V AC, 3 phase
Maximum Voltage Rating	480 V AC
Control Units	Selector switch HAND-OFF-AUTO) Push-button START)
Disconnect Type	Fusible disconnect switch
Associated fuse rating	400 A
Fuse type	H or K
Thermal overload type	Motor Logic solid state class 10/20
Protection Type	Overload Phase loss Phase unbalance
Device mounting	Surface
Electrical Connection	Screw terminal
NEMA size	6
Height	93.0 in (2362 mm)
Width	36.0 in (914 mm)
Depth	19.3 in (489 mm)

Environment

NEMA Rating	NEMA 3R
Enclosure type	Weatherproof enclosure indoor/outdoor
Product Certifications	UL Listed NEMA

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ordering and shipping details

Category	US10CP121394
Discount Schedule	0CP1
GTIN	785901716983
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	92.99 in (236.2 cm)
Package 1 Width	35.98 in (91.4 cm)
Package 1 Length	19.25 in (48.9 cm)
Package 1 Weight	875.0000000000 lb(US) (396.893 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	Yes
EU RoHS Directive	Under investigation
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

 Repack and remanufacture	
Take-back	No