

# Product data sheet

Specifications



Cable end, Linergy TR cable ends, single conductor, red, 35 mm<sup>2</sup>, medium size, clipin tag holder, 10 sets of 100

DZ5CA352

## Main

|                           |                    |
|---------------------------|--------------------|
| Range of product          | Linergy            |
| Product or component type | Cable end          |
| Cable end size            | Medium             |
| Standards                 | NF C 63-023        |
| Type of packing           | Bag                |
| Quantity per set          | Set of 20          |
| Cable cross section       | 35 mm <sup>2</sup> |

## Complementary

|                        |                                  |
|------------------------|----------------------------------|
| Cable end type         | Single conductor                 |
| Additional information | For additional marker tag holder |
| Colour                 | Red                              |
| Bezel material         | Halogen-free plastic             |
| Tube material          | Copper conforming to ISO 1337    |
| Number of cables       | 1                                |
| AWG gauge              | AWG 2                            |
| Bezel size             | Ø 13.5 mm                        |
| Tube diameter          | 8.7 mm                           |
| Length                 | 30 mm                            |
| Tube length            | 16 mm                            |
| CAD overall depth      | 30 mm                            |
| Product weight         | 0.054 kg                         |

## Environment

|                                       |              |
|---------------------------------------|--------------|
| Ambient air temperature for operation | -20...105 °C |
|---------------------------------------|--------------|

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Height             | 0.400 cm |
| Package 1 Width              | 0.400 cm |
| Package 1 Length             | 1.400 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                              |           |
|------------------------------|-----------|
| Package 1 Weight             | 1.500 g   |
| Unit Type of Package 2       | BB1       |
| Number of Units in Package 2 | 20        |
| Package 2 Height             | 1.500 cm  |
| Package 2 Width              | 10.000 cm |
| Package 2 Length             | 14.000 cm |
| Package 2 Weight             | 31.000 g  |
| Unit Type of Package 3       | S02       |
| Number of Units in Package 3 | 1500      |
| Package 3 Height             | 15.000 cm |
| Package 3 Width              | 30.000 cm |
| Package 3 Length             | 40.000 cm |
| Package 3 Weight             | 2.646 kg  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

| Environmental footprint  |                                               |
|--------------------------|-----------------------------------------------|
| Environmental Disclosure | <a href="#">Product Environmental Profile</a> |

Use Better

| Materials and Substances               |                                    |
|----------------------------------------|------------------------------------|
| Packaging made with recycled cardboard | Yes                                |
| Packaging without single use plastic   | No                                 |
| <a href="#">EU RoHS Directive</a>      | Compliant                          |
| REACH Regulation                       | <a href="#">REACH Declaration</a>  |
| Halogen-free status                    | Halogen free plastic parts product |
| PVC free                               | Yes                                |

Use Again

| Repack and remanufacture        |                                                                                                                                                                                                                 |
|---------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| End of life manual availability | <a href="#">End of Life Information</a>                                                                                                                                                                         |
| Take-back                       | No                                                                                                                                                                                                              |
| WEEE Label                      |  The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |