



Main

Product Range	Legacy
Product Type	Socket
Product Compatibility	Relay 788XBXR/XCXR
Number of Terminals	11
Switch Function	3PDT
Contact Composition	3 NO + 3 NC

Complementary

Rated Current	15 A
[Ue] rated operational voltage	300 V
Contact Terminal Arrangement	Mixed
Connections Terminals	Solder terminal
Fixing Mode	By screw chassis By screw panel
Product Weight	0.43 oz (12.1 g)
Width	1.50 in (38.1 mm)
Depth	2.03 in (51.45 mm)

Environment

Ambient Air Temperature for Storage	-40...221 °F (-40...105 °C)
Ambient Air Temperature for Operation	-40...131 °F (-40...55 °C)
IP Degree of Protection	IP20
Flame Retardance	UL94-V0
Product Certifications	UL CSA CE

Ordering and shipping details

GTIN	3606480277757
Nbr. of units in pkg.	1
Package weight(Lbs)	0.43 oz (12.1 g)

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.01 in (5.1 cm)
Package 1 width	1.50 in (3.81 cm)
Package 1 Length	0.64 in (1.617 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	4.27 oz (121.0 g)
Package 2 Height	1.50 in (3.8 cm)

Package 2 width	1.97 in (5 cm)
Package 2 Length	5.51 in (14 cm)
Unit Type of Package 3	CAR
Number of Units in Package 3	1000
Package 3 Weight	26.68 lb(US) (12.1 kg)
Package 3 Height	8.46 in (21.5 cm)
Package 3 width	11.61 in (29.5 cm)
Package 3 Length	20.28 in (51.5 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Approximate Dimensions

