

Product data sheet

Specifications



All in one, Homeline, CSED, ringed socket, 200A, surface mount, 30 spaces, 42 circuits, 22kA SCCR, no bypass, solar ready

SC3042M200PS

Product availability: Stock - Normally stocked in distribution facility

Main

Product or Component Type	All-In-One
Range of Product	Homeline
Meter socket type	Ringed
Hub type	A

Complementary

Line Rated Current	200 A
Short-circuit current	22 kA
Mounting	Surface
Number of spaces	30
Number of circuits	42
Number of Tandem Breakers	12
Electrical connection	Lugs, line side Lugs, service ground
Wire Size	AWG 4...250 kcmil (aluminium/copper) line side AWG 14...AWG 2/0 (aluminium/copper) service ground
Tightening torque	Main lugs 250 lb.in, AWG 4...250 kcmil, aluminium/copper Service ground 50 lb.in, AWG 14...AWG 2/0, copper Service ground 50 lb.in, AWG 12...AWG 2/0, aluminium Branch lugs 50 lb.in, AWG 14...AWG 4, copper Branch lugs 50 lb.in, AWG 12...AWG 2, aluminium Branch lugs 35 lb.in, AWG 6...AWG 4, aluminium/copper Branch lugs 25 lb.in, AWG 8, aluminium/copper Branch lugs 20 lb.in, AWG 14...AWG 10, aluminium/copper Branch lugs 20 lb.in, AWG 12...AWG 10, aluminium/copper Cover 10 lb.in
Disconnect Rating	200 A
Branch Breaker Rating	200 A
Service feed location	OH UG
Bypass type	No bypass
Connections - Terminals	Plug-on neutral
Color	Grey
Product Compatibility	Solar ready
Width	21.50 in (546.10 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Depth	6.30 in (160.02 mm)
Height	32.69 in (830.33 mm)
Bus Rating	225.0 A

Environment

NEMA Rating	NEMA 3R
-------------	---------

Ordering and shipping details

Category	US1DE3A00148
Discount Schedule	DE3A
GTIN	785901219767
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	7.31 in (18.57 cm)
Package 1 Width	21.69 in (55.09 cm)
Package 1 Length	32.63 in (82.88 cm)
Package weight(Lbs)	56.610 lb(US) (25.678 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	10
Package 2 Height	43.50 in (110.49 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	607.00 lb(US) (275.33 kg)

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	426
Environmental Disclosure	Product Environmental Profile

Use Better


Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant with Exemptions
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

Technical Illustration

Dimensions



Technical Illustration

Wiring diagram




Image of product / Alternate images

Alternative

