

AR3104SP1

APC NetShelter SX, Server Rack Enclosure,
24U, Shock Packaging, 1250 lbs, Black, 1200H
x 600W x 1070D mm



Overview

Presentation	NetShelter SX cabinet and packaging system designed to safely integrate, transport, unload and deploy up to 1250 lbs (566 kg) of IT equipment. The cabinet is paired with a shock absorbing pallet, unloading ramp, and impact resistant shell. The system has been engineered, tested and approved for secure shipment of fully converged systems such as being certified with Cisco® for pre-racking and shipping Cisco Unified Computing System (UCS).
Lead time	Usually in Stock

Main

Number of rack unit	24U
Provided equipment	Baying hardware Doors Installation guide Keyed-alike doors and side panels Leveling feet Mounting Hardware Pallet ramps Pre-installed casters Reusable packaging Roof Side Panels

Physical

Color	Black
Height	47.24 in (120 cm)
Width	23.62 in (60 cm)
Depth	42.13 in (107 cm)
Net Weight	196.41 lb(US) (89.09 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	36.02 in (91.49 cm)
Minimum Mounting Depth	7.52 in (19.1 cm)
Rack Width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels
Permanent permissible load	2250 Lb(US) (1020.58 kg) dynamic 3000 lb(US) (1360.78 kg) static

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

Ordering and shipping details

GTIN	731304262275
Package weight(Lbs)	235.50 lb(US) (106.82 kg)

Packing Units

Package 1 Height	53.15 in (135 cm)
Package 1 width	35.39 in (89.9 cm)
Package 1 Length	47.99 in (121.9 cm)
Number of Units in Package 3	1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------