



Powering Business Worldwide

TRIPP LITE
SERIES

Ultra Thin Toslink to Mini Toslink Digital Optical SPDIF Audio Cable, 2M (6.56 ft.)

MODEL NUMBER: **A104-02M**



Features

- Connect your digital audio equipment to your home theater system
- Ultra Thin cable is ideal for situations where space is at a premium
- Digital Optical Fiber offers the best in Audio clarity
- Precision polished optical termination minimizes loss for better high frequencies, and a more realistic stereo image
- Immune to all Electromagnetic and Radio-Frequency interference
- Eliminates distortion caused by inductance, capacitance, and resistance found in copper cables

Specifications

OVERVIEW	
UPC Code	037332189080
Technology	Stereo Audio; Toslink/SPDIF
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	TOSLINK (MALE)
Side B - Connector 1	MINI TOSLINK (MALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Cable Jacket Color	Black

Highlights

- Connect your digital audio equipment to your home theater system
- Ultra Thin cable is ideal for situations where space is at a premium
- Superior-grade optical fiber and precision polished optical terminations
- Best possible sound quality through digital fiber optic signals
- Immune to all forms of EMI/RFI

System Requirements

- Home Theater or Stereo equipment with Toslink/Mini Toslink capabilities

Package Includes

- 2M (6.6-ft.) Ultra Thin Toslink to Mini Toslink Digital Optical Audio Cable



Powering Business Worldwide

TRIPP LITE
SERIES

Cable Length (ft.)	6.6
Cable Length (m)	2.01
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.04
Shipping Weight (kg)	0.02
Unit Dimensions (hwd / in.)	9.000 x 7.000 x 0.500
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.