

Dual-Display Desktop Monitor Stand for 13" to 27" Flat-Screen Displays

MODEL NUMBER: DDR1327SDD



Mounts two monitors on a single base to free up valuable space on your desk, table or work area.

Features

2-Screen Monitor Stand Lifts Your Displays Above Your Work Area's Surface

This VESA-compliant display stand mounts two flat-screen monitors on a sturdy base, allowing you to free up valuable workspace on your desk, table or workstation. Recommended for home or office use, the DDR1327SDD fits most flat-panel monitors from 13 to 27 inches and supports up to 26 pounds (11.8 kilograms) per VESA mount.

Swivel, Tilt and Rotate the Screen to Find the Perfect and Most Comfortable Viewing Angle

This desk mount for your computer monitors adjusts independently to optimize viewing angles, minimize glare and improve ergonomics. To minimize screen glare, reduce eye fatigue and increase viewing comfort, the mount features -45° to +45° tilt, -90° to +90° swivel and 360° rotation for positioning your screen in portrait or landscape orientation. Easy screen adjustment lets you quickly find just the right angle without interrupting your workday. A heavy-duty base keeps the freestanding mount stable on a desk or table during adjustment.

VESA-Compliant Mounting Ensures Display Compatibility

VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for TVs and monitors. For hassle-free display compatibility, this monitor stand supports the following VESA mounting hole patterns: 75 x 75, 75 x 100, 100 x 75 and 100 x 100. Mounting hardware is included.

Sure to Stand Up to Frequent Use

The durable steel frame withstands the stress of repeated adjustments. Its scratch-resistant powder-coated finish tolerates frequent handling and blends easily into any home or office décor. Monitor cables clip to the stand to eliminate clutter and keep your work area organized.

Highlights

- Monitor mount with heavy-duty base remains stable on your desk during adjustment
- -45° to +45° tilt, -90° to +90° swivel and 360° rotation helps you find the perfect angle
- Durable steel construction blends into any décor and supports up to 26 lb. per mount
- Display cables attach to pole to reduce clutter and keep cords organized
- VESA compliance ensures compatibility with common mounting patterns

Package Includes

- Pole
- Base
- (2) Mounting arms
- Locking head assembly
- Pole cable guide
- Base collar
- (2) VESA plate assemblies
- (2) Arm cable guides
- (2) End caps
- (8) Washers
- (18) Screws
- Hex key, 3 mm
- Hex key, 4 mm
- Hex key, 6 mm
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332203397
Device Compatibility	Monitor/HDTV



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	100x100; 100x75; 75x100; 75x75
Motion	Full
Mounting Location	Desktop
Degrees of Motion	-45/+45 Tilt; 180 Swivel; 360 Rotate
Minimum Screen Size (in.)	13
Minimum Screen Size (cm)	33.02
Maximum Screen Size (in.)	27
Maximum Screen Size (cm)	68.58
Maximum Weight Capacity (lbs.)	26
Maximum Weight Capacity (kg)	12
Number of Displays	2
Shipping Dimensions (hwd / in.)	12.83 x 18.11 x 5.20
Shipping Dimensions (hwd / cm)	32.59 x 46.00 x 13.21
Shipping Weight (lbs.)	12.76
Shipping Weight (kg)	5.79
Unit Dimensions (hwd / in.)	18.110 x 31.690 x 10.000
Unit Dimensions (hwd / cm)	46.0 x 80.5 x 25.4
Unit Weight (lbs.)	10.56
Unit Weight (kg)	4.79
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	Yes
Tools Necessary	Yes
Security Lock	No
Height Adjustable	No
Outdoor Use	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; RoHS3; REACH
WARRANTY & SUPPORT	



Powering Business Worldwide

TRIPP LITE
SERIES

Product Warranty Period (Worldwide)	5-year limited warranty
Product Warranty Period (U.S. & Canada)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.