



Powering Business Worldwide

Wireless Access Point Enclosure - NEMA 4, Surface-Mount, PC Construction, 13 x 9 in.

MODEL NUMBER: EN1309N4



Protects your indoor or outdoor Wi-Fi access point against water, dust, rain, sleet, snow and ice, as well as theft, damage or tampering.

Features

Wall-Mount Enclosure Secures and Organizes Your Router/Modem or Wireless Access

Point Protect your indoor or outdoor router/modem or Wi-Fi access point by installing it inside this SmartRack® NEMA 4 Wireless Access Point Enclosure made from impact-resistant UL 94 V-1 Classified PC plastic. It's ideal for offices, dorms, hotels, classrooms, retail locations and other indoor/outdoor areas where you need to keep Wi-Fi equipment secure, organized and out of the way.

Carries a NEMA 4 Rating for Protection Against Harsh Elements The NEMA 4-rated enclosure supports indoor or outdoor use. It protects its contents against the ingress of water (including rain, sleet, snow, splashing water and hose-directed water), solid foreign objects (including falling dirt and windblown dust) and even ice forming on the outside of the enclosure.

Accommodates a Wide Range of Equipment, Including Cisco WAPs, up to 468 in.³ Though the EN1309N4 is designed specifically to protect Cisco Wi-Fi access points, it will also house most other equipment up to 468 cubic inches (7669 cubic centimeters). While rugged enough to keep your equipment safe inside, it's also transparent to wireless signals, ensuring strong Wi-Fi coverage. The polycarbonate plastic cover attaches to the enclosure with the included screws to protect the contents against theft or tampering.

Supports Wall- or Ceiling-Mounting to Best Fit Your Application The EN1309N4 comes fully assembled and ready for horizontal or vertical mounting on a wall or ceiling with user-provided hardware. It is designed for Cisco WAPs, but the included universal T-bar bracket will accommodate a wide variety of equipment from other brands.

Highlights

- Designed for Cisco WAPs, but accommodates equipment from most vendors
- NEMA 4 rating ensures protection against water, dust, rain, sleet, snow and ice
- Rugged polycarbonate housing protects router/modem/WAP from theft or tampering
- Transparent to wireless signals, ensuring an optimum Wi-Fi signal in all directions
- Comes fully assembled and ready for wall- or ceiling-mounting using included hardware

Applications

- Protect a router/modem or wireless access point inside a classroom, office, hotel, store, dorm or other indoor space from damage, theft or tampering
- Protect outdoor equipment against water, dust, rain, sleet, snow and ice

Package Includes

- NEMA 4 wireless access point enclosure, 13 x 9 in.
- (4) M4 screws
- (2) M6 screws, 1 in.
- (2) M6 trusshead screws, 0.25 in.
- (4) M6 flathead screws, 0.25 in.
- Cable tie
- (4) Nylon spacers
- T-bar bracket
- Installation guide

Specifications

OVERVIEW	
UPC Code	037332217837
Rack Type	Enclosure



Powering Business Worldwide

PHYSICAL	
Color	White
Material of Construction	UL 94 V-1 Classified PC Plastic
Rack Height	0U
Maximum Device Depth (cm)	9.65
Maximum Device Depth (in.)	3.8
Maximum Device Depth (mm)	97
Shipping Dimensions (hwd / in.)	14.06 x 9.88 x 5.47
Shipping Dimensions (hwd / cm)	35.71 x 25.10 x 13.90
Shipping Weight (kg)	1.90
Unit Dimensions (cm)	33.99 x 71.628
Unit Dimensions (hwd / in.)	13.380 x 9.060 x 4.000
Unit Dimensions (hwd / cm)	33.99 x 71.628 x 10.6
Unit Dimensions (in.)	13.38 x 9.06
Unit Weight (lbs.)	3.3
Unit Weight (kg)	1.50
Interior Dimensions (hwd / in.)	10.94 x 8.60 x 2.06
Interior Dimensions (hwd / mm)	277.99 x 218.50 x 52.40
FEATURES & SPECIFICATIONS	
Built-in Cable Management	No
STANDARDS & COMPLIANCE	
Product Compliance	NEMA 4; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.