

Product data sheet

Specifications



All in one, Homeline, CSED, ringed socket, 125A, surface mount, 16 spaces, 24 circuits, 10kA SCCR, no bypass

SC1624M125S

Product availability: Stock - Normally stocked in distribution facility

Main

Product or Component Type	All-In-One
Range of Product	Homeline
Meter socket type	Ringed
Hub type	A

Complementary

Line Rated Current	125 A
Short-circuit current	10 kA
Mounting	Surface
Number of spaces	16
Number of circuits	24
Number of Tandem Breakers	8
Electrical connection	Lugs, line side Lugs, service ground
Wire Size	AWG 6...AWG 2/0 (aluminium) line side AWG 6...AWG 2/0 (copper) line side AWG 6...AWG 2/0 (aluminium) service ground AWG 6...AWG 2/0 (copper) service ground
Disconnect	Service disconnect (factory installed)
Disconnect Rating	125 A
Branch Breaker Rating	125 A
Service feed location	OH UG
Bypass type	No bypass
Width	14.77 in (375.16 mm)
Depth	5.20 in (132.08 mm)
Height	26.50 in (673.10 mm)
Bus Rating	125.0 A

Ordering and shipping details

Category	US1DE3A00148
Discount Schedule	DE3A
GTIN	785901308829

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	6.20 in (15.748 cm)
Package 1 Width	15.10 in (38.354 cm)
Package 1 Length	26.40 in (67.056 cm)
Package weight(Lbs)	31.500 lb(US) (14.288 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	18
Package 2 Height	40.00 in (101.600 cm)
Package 2 Width	40.00 in (101.600 cm)
Package 2 Length	48.00 in (121.920 cm)
Package 2 Weight	567.0007 lb(US) (257.187 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	378
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

Technical Illustration

Dimensions

Technical Illustration

Wiring diagram

Image of product / Alternate images

Alternative

