



Powering Business Worldwide

End-of-Row Door for RapidPod Aisle Containment System - Single Swing, 90”H x 36”W, TAA

MODEL NUMBER: NXEORDSH9036



Blocks escape routes for air and eliminates air recirculation and mixing in your modular RapidPod Aisle Containment System.

Features

Modular Customization of Your RapidPod Aisle Containment System

This end-of-row door (EoRD) optimizes airflow management in your RapidPod® Aisle Containment System by sealing off key air escape routes, which reduces air recirculation and air mixing. This allows for higher ambient temperatures, which lowers your energy costs and extends the life of the valuable equipment in your high-performance data center.

Designed for Convenience and Durability

The single-swing door is easy to install, which means very little downtime and disruption in your active data center. The field-reversible design supports either left-hand or right-hand swinging configurations for convenient installation options. Also included are ceiling-mount provisions for threaded rod installation, ensuring secure overhead support.

A Practical, High-Performance Solution for Aisle Containment

The fully transparent and impact-resistance window boasts a stringent UL94 V-0 rating for the utmost safety and visibility. A secure grabber latch keeps the door firmly closed to maintain optimal thermal conditions within the aisle or holds the door open to make equipment handling and maintenance easily accessible. An integrated edge grip seal at the bottom of the door seals air gaps to maintain blockage.

TAA-Compliant for GSA Schedule Purchases

The NXEORDSH9036 is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Highlights

- Field-reversible design supports either left- or right-hand swinging configurations
- Fast, hassle-free installation minimizes downtime and disruption in a busy data center
- Fully transparent, impact-resistance window rated UL94 V-0 for safety and visibility
- Secure grabber latch keeps doors firmly closed to maintain contained airflow
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

End-of-row door, single swing, 90 x 36 in.

Specifications

OVERVIEW	
UPC Code	037332301178
Aisle Containment System Component Type	Door Kit



Powering Business Worldwide

PHYSICAL	
Color	Black; Gray
Unit Dimensions (hwd / in.)	90.000 x 36.000 x 3.600
Unit Dimensions (hwd / cm)	90H 36W
Unit Weight (lbs.)	50
Unit Weight (kg)	22.68
Rack Compatibility	300 mm (In-Row Cooler); 600 mm (Standard); 750 mm (Wide)
FEATURES & SPECIFICATIONS	
Built-in Cable Management	No
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.