

PS/2 (3-in-1) Cable Kit for KVM Switch B004-008, 15 ft. (4.57 m)

MODEL NUMBER: **P750-015**



Highlights

- Connects a PS/2 Computer to a B004-008 KVM Switch
- 3-in-1 construction and slim size makes management and organization of cables much easier
- Molded, color-coded connectors

System Requirements

- A PS/2 computer or an adapter (model # B015-000) for a non-PS/2 computer.
- 8-port KVM switch, B004-008

Package Includes

- 15-ft. (4.57 m) PS/2 (3-in-1) KVM Cable Kit

Description

This PS/2 (3-in-1) KVM cable kit is designed to connect a PS/2 computer to a B004-008 Standard 8-Port KVM Switch. This premium 3-in-1 cable provides superior performance and cable management. The KVM Switch side of the cable kit consists of a HD15 Male cable. The Computer side of the cable kit consists of a PS/2 (MiniDIN6) Male Mouse cable, a PS/2 (MiniDIN6) Male Keyboard cable and a HD15 Male cable. This low profile cable kit is incredibly flexible, making cable management a breeze. All cables are manufactured from superior molded cable with integral strain relief and foil shielding for maximum EMI/RFI protection.

Features

- Connects a PS/2 computer to a B004-008 8-Port KVM Switch.
- KVM Switch side of the cable kit consists of a HD15 Male cable
- Computer side of the cable kit consists of a PS/2 (MiniDIN6) Male Mouse cable, a PS/2 (MiniDIN6) Male Keyboard cable and a HD15 Male cable
- Provides superior performance and cable management
- Low profile cable is super flexible and easy to control
- Superior molded cable with integral strain relief and double shielding (foil and braid) for maximum EMI/RFI protection

Specifications

OVERVIEW	
UPC Code	037332125347
Accessory Type	Cable Kit
Technology	PS/2; VGA/SVGA
Accessory Class	KVM Switch Accessories
PHYSICAL	



Powering Business Worldwide

TRIPP LITE
SERIES

Cable Length (ft.)	15
Cable Length (m)	4.57
Shipping Dimensions (hwd / in.)	11.00 x 6.50 x 0.50
Shipping Dimensions (hwd / cm)	27.94 x 16.51 x 1.27
Shipping Weight (lbs.)	0.75
Shipping Weight (kg)	0.34
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.