

Safe-IT Mounting Clamp for Medical-Grade Power Strips - Antimicrobial Protection

MODEL NUMBER: PSCLAMP2



Mounts a medical-grade power strip or surge protector to an IV pole, crash cart or anywhere else needing portable power.

Features

Permanently Mounts a Power Strip or Surge Protector in Your Healthcare Facility Safely attach a medical-grade power strip or surge protector to an IV pole, hospital bed, crash cart, mobile medical workstation, hospital bed rail, crib or anywhere else needing portable power. The PSCLAMP2's drip shield protects outlets from falling liquids and other contaminants that could damage the power strip or connected equipment. A built-in cord management system keeps the power strip's cabling organized and safely out of the way when not in use to reduce tripping hazards.

Exclusive Antimicrobial Protection Fights Healthcare-Acquired Infections (HAIs) The mounting clamp is protected by an antimicrobial powder coating with EPA-registered and FDA-compliant silver ionic technology. The antimicrobial surface protection is effective in inhibiting the growth of bacteria and reducing the risk of HAIs in hospitals and other medical environments. The coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

Works with Nearly All Brands of Power Strip All necessary hardware is included for mounting the lightweight aluminum PSCLAMP2 to pole diameters from .875 inches to 1.25 inches. It not only mounts line of medical-grade power strips, but those of other brands as well, bringing power to areas where wall outlets are scarce or impractical. The clamp is designed to last within busy medical environments and stand up to heavy use.

Specifications

OVERVIEW	
UPC Code	037332225481
Accessory Type	Mounting Accessories
Accessory Class	Power Strip Accessories
INPUT	

Highlights

- Antimicrobial protection helps prevent the growth of bacteria, viruses, fungi, mold and mildew
- Durable lightweight aluminum construction designed to stand up to heavy use
- Built-in drip shield protects outlets from liquid and other contaminants
- Mounting hardware included for quick, easy installation on IV pole, crash cart or bed
- Adjustable clamp fits poles ranging in diameter from .875 in. to 1.25 in.

Package Includes

- (2) Mounting brackets
- (2) Retainer brackets
- (2) M6 Phillips-head screws, 12 mm
- (4) M5 Phillips-head screws, 30 mm
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

Input Cord Length (ft.)	0
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Output Receptacles	Universal outlets
Right-Angle Outlets	No
PHYSICAL	
Color	White
Material of Construction	Metal
Mounting Holes or Slots	No
Cable Management	Bar
Shipping Dimensions (hwd / in.)	3.03 x 6.22 x 10.75
Shipping Weight (kg)	0.42
Unit Dimensions (hwd / in.)	0.530 x 3.030 x 6.220
Unit Weight (lbs.)	0.530
Unit Weight (kg)	0.24
FEATURES & SPECIFICATIONS	
Antimicrobial	Yes
Antibacterial	No
Built-in Cable Management	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.