

4-Post Rack-Mount Installation Kit of select Rack-Mount UPS Systems

MODEL NUMBER: 4POSTRAILKIT



Highlights

- Supports UPS systems in 4-post rackmount applications
- Adjustable to any setting between 20.5 and 36 inches
- Temporary placement pegs simplifies single-person installation
- Square hole rack attachment hardware included
- Supports UPS chassis up to 250 lbs (113.4 kgs)

Package Includes

- Pair of expandable L brackets
- Attachment hardware

Description

The 4POSTRAILKIT adjustable rack-mount shelf system supports heavy UPS systems in 4-post rack-mount applications. Includes one pair of expandable "L bracket" mounting rails to offer front-to-rear support of rack-mount UPS systems. Pair of expandable "L brackets" adjust to any setting between 20.5 and 36 inches. Includes mounting hardware compatible with square-hole racks. Set of temporary placement pegs enables simple single-person installation by allowing the rails to be held in place while attachment hardware is installed. Also compatible with other heavy pieces of networking or power protection equipment with 17.5-inch-wide rectangular chassis. Supports up to 250 pounds (113.4 kilograms).

Features

- 4POSTRAILKIT adjustable rack-mount shelf system supports heavy UPS systems in 4-post rack-mount applications
- Includes one pair of expandable "L bracket" mounting rails to offer front to rear support rack-mount UPS systems
- Pair of expandable "L brackets" adjust to any setting between 20.5 and 36 inches
- Includes mounting hardware compatible with square-hole racks
- Set of temporary placement pegs enables simple single-person installation by allowing the rails to be held in place while attachment hardware is installed
- Also compatible with other heavy pieces of networking or power protection equipment with 17.5 inch wide rectangular chassis
- Supports up to 250 pounds (113.4 kg)

Specifications

OVERVIEW	
UPC Code	037332148865
Accessory Type	Rackmount Kit
Accessory Class	UPS Accessories



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Shipping Dimensions (hwd / in.)	3.00 x 22.40 x 4.90
Shipping Dimensions (hwd / cm)	7.62 x 56.90 x 12.45
Shipping Weight (lbs.)	6.60
Shipping Weight (kg)	2.99
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Weight Capacity - Stationary (kg)	113
Weight Capacity - Stationary (lbs.)	250
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.