



Powering Business Worldwide

480V Extended Battery Module (EBM) for Select Eaton 93PX 3-Phase UPS Systems, 6U

MODEL NUMBER: 93PX2EBM480U



Provides extended runtime for compatible 93PX 3-phase UPS systems used in mission-critical edge and data center applications.

Features

Backup Battery Module Gives Your Compatible Eaton UPS System Extended Runtime

The 93PX2EBM480U offers extended battery runtime when used in conjunction with Eaton's 93PX 3-phase UPS systems. It can also be daisy-chained for a maximum of four auto-detected pairs of 3U extended battery modules (EBMs) to deliver even longer extended-run operation. Heavy-gauge cabling with high-current DC connectors is included for safe, simple installation.

Innovative Quick-Connect Design for Easy Plug-and-Play Deployment and Service

Interconnections between the 93PX2EBM480U, UPS power module(s) and a maintenance bypass panel provide easy plug-and-play setup and serviceability. You can mount all UPS modules in an EIA-standard 19-inch rack using the included hardware, and connect the modules together using the included cables.

Highlights

- Includes one pair of 3U EBMs combined in one 6U application
- Connects to select expandable Eaton 93PX UPS systems for extended runtime
- Daisy-chain connector supports additional battery packs for even longer runtime
- Comes with heavy-gauge cabling with high-current 480V DC connectors
- Innovative quick-connect design for easy plug-and-play deployment and service

Package Includes

- 93PX2EBM480U 6U extended battery module (one pair of 3U EBMs)
- Rack-mounting hardware
- Assorted cabling
- User documentation

Specifications

OVERVIEW	
UPC Code	037332296023
Accessory Type	Battery
Accessory Class	UPS Accessories
INPUT	
Nominal Input Voltage(s) Supported	400V AC
OUTPUT	
Output Capacity (kVA)	0
Nominal Output Voltage(s) Supported	230/400V 3-PH Wye



Powering Business Worldwide

BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
PHYSICAL	
Unit Dimensions (hwd / in.)	5.080 x 17.240 x 27.280
Unit Weight (lbs.)	157.6
Unit Weight (kg)	71.49
STANDARDS & COMPLIANCE	
Product Certifications	IEC 62040-2; UL 1778
Product Compliance	FCC Part 15 Class B (USA)
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.