


SmartRack 3U Rack-Mount Configurable Storage Shelf for Personal Electronics

MODEL NUMBER: **SR16SHELF**



Securely stores up to 16 personal electronic devices in your wall-mount or floor rack enclosure.

Description

The SR16SHELF 3U Rack-Mount Configurable Storage Shelf securely stores up to 16 personal electronic devices in your wall-mount or floor rack enclosure. Ideal for storing tablets, laptops, Chromebooks and other similar devices, the SR16SHELF comes preset with 0.8 inches of spacing between its plastic dividers. However, the 15 dividers can easily be removed and adjusted to fit your devices. Compatible with all EIA-compliant 19-inch wall-mount and floor rack enclosures, the SR16SHELF is covered in non-scuff paint designed to resist scratches. The devices' charging cables pass through ports with rubber grommets that hold the cable in place and prevent clutter and tangles. All mounting hardware included. Mounts into 3U of rack space, but may require additional rack space depending on the size of the devices being stored.

Features

Stores Up to 16 Personal Electronic Devices Ideal for storing tablets, laptops, Chromebooks, Ultrabooks, MacBook Airs and other similar devices
Includes 15 removable plastic dividers preset with 0.8 inches of spacing between them
Dividers can easily be adjusted to fit devices

Mounts in 3U of Rack Space Fits all EIA-compliant 19 in. wall-mount and floor rack enclosures
May require additional rack space depending on size of the devices being stored
Non-scuff paint resists scratches
Cable ports with rubber grommets that hold charging cables in place and prevent clutter and tangles
Mounting hardware included

Specifications

OVERVIEW	
UPC Code	037332188748
Accessory Type	Rack Shelves
Accessory Class	Rack Accessories
PHYSICAL	

Highlights

- Removable plastic dividers easily adjust to your preference
- Non-scuff scratch-resistant paint protects your devices
- Cable ports with grommets hold charging cables in place
- Mounting hardware included
- Compatible with EIA-compliant 19 in. wall-mount and floor racks

Package Includes

- SR16SHELF 3U Rack-Mount Configurable Storage Shelf
- (15) Plastic dividers
- (8) M6 screws
- (8) M6 cage nuts
- (8) M6 cup washers
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

Color	Black
Shipping Dimensions (hwd / in.)	8.00 x 19.20 x 20.80
Shipping Dimensions (hwd / cm)	20.32 x 48.77 x 52.83
Shipping Weight (lbs.)	15.60
Shipping Weight (kg)	7.08
Unit Dimensions (hwd / in.)	4.880 x 18.880 x 15.810
Unit Dimensions (hwd / cm)	12.40 x 47.96 x 40.16
Unit Weight (lbs.)	12.00
Unit Weight (kg)	5.44
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.