



Cable Ladder, 2 Sections - SRCABLETRAY or SRLADDERATTACH Required, 10 x 1.5 ft. (3 x 0.3 m)

MODEL NUMBER: SRCABLELADDER18



Provides roof-mounted cable routing for Tripp Lite SmartRack® enclosures, allowing cable bundles to span aisles or spaces between racks.

Features

Eliminate Cable Stress by Organizing Cabling Outside Your Enclosure or Open Frame RackThe SmartRack SRCABLELADDER18 mounts to the top of your rack enclosure or open frame rack for overhead cable routing. Install it either parallel or perpendicular to the rack for clean, organized cable routing across an aisle or within a row. Each SRCABLELADDER measures 10-ft. (3.05 m) long and 1.5-ft. (0.45 m) wide for safe cable bundling. It requires the use of SRCABLETRAY (for enclosures) or SRLADDERATTACH (for open frame racks) for installation (both accessories sold separately). An included grounding stud allows tie-in to the rack and facility ground. The SRCABLELADDER18 ships in two 5-ft. (1.52 m) sections for convenient storage and assembly.

Highlights

- Cuts cable clutter by routing cable bundles overhead in your data center
- Allows cables to span aisles or spaces between racks in the same row
- Measures 10 ft. long and 1.5 ft. wide for organized cable bundling
- Arrives boxed in dual 5 ft. sections for easy shipping, storage and assembly
- Works in tandem with SRCABLETRAY or SRLADDERATTACH (sold separately)

Applications

- Neatly bundle cable across an aisle or within a row of bayed racks in your data center

System Requirements

- SRCABLETRAY (rack enclosures) or SRLADDERATTACH (open frame racks)

Package Includes

- (2) Ladder sections
- (4) Assembly brackets
- (8) Clevis pins
- (8) Cotter pins
- (2) Ground brackets
- (2) M6 hex bolts
- (3) Ground cables, 2-ft. (0.61 m)
- (4) Ladder clamps
- (4) M6 lock washers
- (2) M6 hex nuts
- (2) M10 x 60 mm carriage bolts
- (2) M10 lock washers
- (2) M10 hex nuts
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332214614



Powering Business Worldwide

TRIPP LITE
SERIES

Accessory Type	Cable Management Accessories
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Shipping Dimensions (hwd / in.)	3.35 x 18.90 x 60.12
Shipping Dimensions (hwd / cm)	8.51 x 48.01 x 152.70
Shipping Weight (lbs.)	21.56
Shipping Weight (kg)	9.78
Unit Dimensions (hwd / in.)	2.000 x 122.300 x 17.920
Unit Dimensions (hwd / cm)	3.81 x 45.72 x 299.72
Unit Weight (lbs.)	18
Unit Weight (kg)	8.16
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.