

## Safe-IT Adjustable Monitor Stand for 17 to 32-inch Displays, Antimicrobial

MODEL NUMBER: **DDV1732AM**



Steel desk mount adjusts your 17 to 32 in. monitor to a comfortable height to free up valuable space on your desk or work area.

### Features

#### Desktop Monitor Mount Lifts Your Display Above Your Work Area's Surface

This Safe-IT™ desk mount raises your display above your desk, table or workstation, allowing you to free up valuable surface space. Recommended for home or office use, the DDV1732AM fits most flat-screen and curved-screen monitors from 17 to 32 inches. The durable steel frame and handle tolerate frequent adjustments, and the premium coil spring supports displays up to 15.4 pounds (7 kilograms). All hardware is included.

#### Swivel, Tilt and Rotate the Dual Screens to Find the Most Comfortable Viewing Angles

The premium coil helical spring adjusts effortlessly to optimize viewing angles, minimize glare and improve ergonomics. To minimize screen glare, reduce eye fatigue and increase viewing comfort, the mount features tilt, swivel and 360° rotation for positioning your screens. Easy screen adjustment lets you quickly find just the right angles without interrupting your workday. Base rotates +/-40 degrees for optimal viewing and information sharing

#### VESA-Compliant Mounting Ensures Display Compatibility

VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for television sets and monitors. For hassle-free display compatibility, this desktop monitor stand supports the following VESA mounting hole patterns: 75 x 75 and 100 x 100. Monitor cables route through a slot to eliminate clutter and keep cords hidden and organized.

#### Antimicrobial Protection Helps Provide a Safer, Cleaner and Healthier Environment

The DDV1732AM comes with a strip of antimicrobial tape, which you can apply to the handle for additional protection against the growth of bacteria, viruses, fungi, mold and mildew.

## Specifications

OVERVIEW	
UPC Code	037332268259
Device Compatibility	Laptop; Monitor/HDTV

### Highlights

- Premium coil helical spring allows effortless adjustment with the featured handle
- Adjustable steel mount supports most 17-32 in. monitors up to 15.4 lb.
- Tilt, swivel and 360° rotation for portrait or landscape help you find the perfect angle
- Rotating base provides easy information or workspace sharing
- Display cables route through convenient slot to eliminate messy cord clutter
- Includes antimicrobial tape for the handle to help protect against bacteria and viruses

### System Requirements

Flat-screen or curved-screen televisions or monitors from 17 to 32 in.

### Package Includes

- DDV1732AM Precision-Placement Desktop Mount
- Antimicrobial tape
- Assembly hardware
- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

PHYSICAL	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	75x75; 100x100
Motion	Full
Mounting Location	Desktop
Degrees of Motion	-15/+15 Tilt; +/-40 Swivel
Minimum Screen Size (in.)	17
Minimum Screen Size (cm)	43.18
Maximum Screen Size (in.)	32
Maximum Screen Size (cm)	81.28
Maximum Weight Capacity (lbs.)	15.4
Maximum Weight Capacity (kg)	7
Number of Displays	1
Shipping Dimensions (hwd / in.)	17.36 x 10.80 x 3.90
Shipping Dimensions (hwd / cm)	44.09 x 27.43 x 9.91
Shipping Weight (lbs.)	8.68
Shipping Weight (kg)	3.94
Unit Dimensions (hwd / in.)	22.400 x 9.450 x 7.870
Unit Dimensions (hwd / cm)	56.9 x 24 x 19.9
Unit Weight (lbs.)	6.5
Unit Weight (kg)	2.95
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	Yes
Cord Management	Yes
Tools Necessary	Yes
Security Lock	No
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); REACH; RoHS3
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty



*Powering Business Worldwide*

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

TRIPP LITE  
SERIES

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.