Management Interface

The ENVIROSENSE management interface is exclusively used for SNMPWEBCARD based products. You will be able to distinguish its use by the round port on the SNMPWEBCARD-enabled device. Models that support the newer EnviroSense2 sensor modules can be distinguished by a USB-A port in place of the round ENVIROSENSE port. For managing the units containing the round port, recommend using the PowerAlert Console Launcher rather than a web browser. This application enables local access of the PDU using a self-contained, compatible Java Runtime Environment version. The Console Launcher can be downloaded for free at the Management Solutions / Utilities page. Units with the new interface work will with most current web browsers.

EnviroSense Rack Environment Sensor, Temperature, Humidity, Contact-Closure Inputs, TAA

MODEL NUMBER: **ENVIROSENSE**



Monitors temperature, humidity and contact-closure inputs. Requires UPS with SNMPWEBCARD, MONITORED PDU or SWITCHED PDU, TAA Compliant

Description

ENVIROSENSE module (when used with SNMP/Web Cards or Intelligent PDUs) provides remote temperature/humidity monitoring and a dry-contact interface to monitor alarm, security and telecom devices.

Features

- Connects to Internal or External SNMP/Web Cards or Intelligent PDU's
- Allows remote temperature/humidity monitoring in network environments
- Enables monitoring of alarm, security and telecom devices through a dry-contact interface
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Highlights

- Environmental Sensor for use with SNMPWEBCARD enabled UPS systems, Monitored PDUs and Switched PDUs
- Reports on the contact closure status of up to four compatible devices (such as smoke detectors, fire alarms and security systems)
- Simple installation
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- ENVIROSENSE
- Manual

Specifications

OVERVIEW	
UPC Code	037332043412

PHYSICAL	
Shipping Dimensions (hwd / in.)	1.60 x 6.10 x 6.10
Shipping Dimensions (hwd / cm)	4.06 x 15.49 x 15.49
Shipping Weight (lbs.)	0.70
Shipping Weight (kg)	0.32
COMMUNICATIONS	
Product Compatibility	SNMPWEBCARD
FEATURES & SPECIFICATIONS	
Sensing Capability	Temperature; Humidity
Contact Closure Capability	Contact Closure Input Monitoring
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
https://tripplite.eaton.com

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.