



## SmartRack 3-in. (7.62 cm) Wide High Capacity Vertical Cable Manager - Double finger duct

MODEL NUMBER: SRCABLEVRT3



### Highlights

- Vertical Cable Manager, 6-ft. (1.83 m), finger duct with cover
- High Capacity (3-in. (7.62 cm) width) for large cable bundles
- Split into three 2-ft. (0.61 m) sections to allow for multiple installation options
- Helps eliminate cable stress
- Organizes cables within SmartRack enclosure
- Toolless button mounts
- Can be used on Open Frame Racks or inside 42U, 45U, and 48U Enclosures

### Package Includes

- Vertical Cable Manager, 6-ft. (1.83 m), finger duct with cover, mounting hardware

### Description

The SmartRack® SRCABLEVRT3 helps eliminate cable stress by organizing the cables within the enclosure. The vertical cable manager (finger duct with cover) is 6 feet (1.8 meters) high, 3 inches (7.6 centimeters) wide and split into three 2-foot (0.6-meter) sections to allow for multiple installation options. SRCABLEVRT3 offers toolless button mounting.

### Features

- SmartRack SRCABLEVRT3 helps eliminate cable stress by organizing the cables within the SmartRack enclosure
- The vertical cable manager (finger duct with cover) is 6-ft. (1.83 m) high, 3-in. (7.62 cm) wide and split into three 2-ft. (0.61 m) sections to allow for multiple installation options
- Toolless button mounting

## Specifications

OVERVIEW	
UPC Code	037332161291
Accessory Type	Cable Management Accessories
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	6.30 x 10.40 x 29.00
Shipping Dimensions (hwd / cm)	16.00 x 26.42 x 73.66
Shipping Weight (lbs.)	17.00
Shipping Weight (kg)	7.71
Unit Dimensions (hwd / in.)	24.450 x 4.400 x 5.310



*Powering Business Worldwide*

TRIPP LITE  
SERIES

Unit Dimensions (hwd / cm)	62.10 x 11.18 x 13.49
Unit Weight (lbs.)	5
Unit Weight (kg)	2.27
Cable Manager Form Factor	Vertical
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
IP20 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; EIA/ECA-310-E
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.