


## SmartRack 6-in. (15.24 cm) Wide High Capacity Vertical Cable Manager - Double finger duct with cover

MODEL NUMBER: **SRCABLEVRT6**



### Highlights

- Vertical Cable Manager, 6-ft. (1.83 m), finger duct with cover
- High Capacity (6-in. (15.24 cm) width) for large cable bundles
- Split into three 2-ft. (0.61 m) sections to allow for multiple installation options
- Helps eliminate cable stress
- Organizes cables within an Open Rack
- Toolless button mounts
- Cold rolled steel with black finish

### Package Includes

- Vertical Cable Manager, 6-ft. (1.83 m), finger duct with cover, mounting hardware

### Description

The SmartRack® SRCABLEVRT6 helps eliminate cable stress by organizing the cables within an open rack cabinet. The vertical cable manager (finger duct with cover) is six feet (1.8 meters) high, six inches (15.2 centimeters) wide and split into three two-foot (0.6-meter) sections to allow for multiple installation options. SRCABLEVRT6 offers toolless button mounting.

### Features

- Eliminate cable stress by organizing the cables within the SmartRack Open Rack cabinet
- Vertical cable manager (finger duct with cover) is 6-ft. (1.83 m) high, 6-in. (15.24 cm) wide and split into three 2-ft. (0.61 m) sections to allow for multiple installation options
- Toolless button mounting.

## Specifications

OVERVIEW	
UPC Code	037332159243
Accessory Type	Cable Management Accessories
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	4.90 x 13.40 x 25.00
Shipping Dimensions (hwd / cm)	12.45 x 34.04 x 63.50
Shipping Weight (lbs.)	21.10
Shipping Weight (kg)	9.57



Powering Business Worldwide

TRIPP LITE  
SERIES

Unit Dimensions (hwd / in.)	24.450 x 6.900 x 6.020
Unit Dimensions (hwd / cm)	62.10 x 17.53 x 15.29
Unit Weight (lbs.)	6.28
Unit Weight (kg)	2.85
Cable Manager Form Factor	Vertical
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
IP20 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; EIA/ECA-310-E
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.