

SmartRack 4U Locking Rack-Mount Storage Drawer

MODEL NUMBER: **SRDRAWER4U**



4U drawer mounts in EIA-standard 19 in. 2-post or 4-post rack to store tools, notes, cables, computer discs and other essential rack equipment accessories up to 50 lb.

Description

The SRDRAWER4U SmartRack® 4U Locking Rack-Mount Storage Drawer is a convenient way to keep tools, cables, notes and essential accessories for your rack-mounted equipment at your fingertips. Constructed using cold-rolled steel with a durable black powder-coated finish, this rack-mount drawer has a maximum load capacity of 50 lbs (22.7 kgs).

Recommended for quick storage in your data center, wiring closet, back office or anywhere else you keep rack equipment, the SRDRAWER4U mounts to your EIA-standard 19-inch 2-post or 4-post rack using the included hardware. It locks securely with the included keys to help prevent damage, tampering or theft. When not in use, the 4U drawer slides smoothly into the rack, out of the way until the next time you need a quick screwdriver or patch cable.

Features

Rack-Mount Drawer for Storing Essential Rack Equipment Accessories

- Keeps tools, cables, notes, computer discs, etc. at your fingertips
- Ideal for quick storage in data center, wiring closet and back office racks
- Maximum load capacity of 50 lbs (22.7 kgs)

Heavy-Duty Steel Construction Designed for Long Life

- Made from durable cold-rolled steel with black powder-coated finish
- Slides smoothly out of the way into rack when not in use
- Locks securely with included keys to protect contents

4U Drawer Mounts in EIA-Standard 19 in. 2- or 4-Post Rack

- Mounting hardware included for quick installation

Highlights

- 4U rack-mount drawer with maximum load capacity of 50 lbs (22.7 kgs)
- Locks securely with included keys to protect contents
- Made from cold-rolled steel with black powder-coated finish
- Mounting hardware included for rack installation
- Slides smoothly out of the way into rack when not in use

Package Includes

- SRDRAWER4U SmartRack 4U Locking Rack-Mount Storage Drawer
- (2) Keys
- Rack-mounting hardware
- Installation guide

Specifications



Powering Business Worldwide

TRIPP LITE
SERIES

OVERVIEW	
UPC Code	037332203182
Accessory Type	Rack Shelves
Accessory Class	Rack Accessories
PHYSICAL	
Shipping Dimensions (hwd / in.)	9.66 x 20.87 x 20.28
Shipping Dimensions (hwd / cm)	24.54 x 53.01 x 51.51
Shipping Weight (lbs.)	22.00
Shipping Weight (kg)	9.98
Unit Dimensions (hwd / in.)	1.730 x 19.000 x 28.900
Unit Dimensions (hwd / cm)	17.68 x 43.74 x 45.24
Unit Weight (lbs.)	20.94
Unit Weight (kg)	9.50
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.