


Cable Runway Corner Bracket Kit for 12 in. and 18 in. Ladder Runway, Straight - Hardware Included

MODEL NUMBER: SRLCRNSPPT



Provides structural support and creates a radius for connecting an L-, T- or X-shaped intersection in your custom-designed cable runway.

Features

Cable Ladder Corner Bracket Helps You Create Custom Data-Center Runway Schemes This exclusive SmartRack® Cable Runway Corner Bracket kit creates a secure connection point between two intersecting sections of cable ladder in your server room or data center. This allows you to create a radius for L-, T- or X-shaped intersections of cable runway and shape the direction of cabling to your liking. The corner support adds a radius that further strengthens and supports the runway, allowing for more voluminous and comprehensive runs. Mounting and installation hardware is included. The corner clamp plates are easy to install and fit solid and tubular steel runway measuring 1.5 x 0.375 inches (38 x 9.5 millimeters). The SRLCRNSPPT is designed for SRCABLELADDER, SRCABLELADDER18 and other compatible 12-inch (305-millimeter) and 18-inch (457-millimeter) straight ladder sections.

Highlights

- Securely connects cable management ladders outside an enclosure or open frame rack
- Allows you more flexibility in routing custom cable management schemes
- Compatible with both 12 in. (305 mm) and 18 in. (457 mm) straight ladder sections
- Fits solid and tubular steel runway measuring 1.5 x 0.375 in. (38 x 9.5 mm)
- Includes all necessary mounting and installation hardware for immediate use

Applications

- Organize a ladder runway system with intersecting sections outside your data center's rack enclosure or open frame rack

System Requirements

- Compatible with 12 in. (305 mm) and 18 in. (457 mm) straight ladder sections, including SRCABLELADDER and SRCABLELADDER18

Package Includes

- Corner bracket
- (4) Clamps
- (4) M6 bolts
- (4) M6 split-lock washers
- (4) M6 nuts
- Installation guide

Specifications

OVERVIEW	
UPC Code	037332214607
Accessory Type	Cable Management Accessories
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Shipping Dimensions (hwd / in.)	3.50 x 17.30 x 17.30



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Dimensions (hwd / cm)	8.89 x 43.94 x 43.94
Shipping Weight (lbs.)	2.48
Shipping Weight (kg)	1.12
Unit Dimensions (hwd / in.)	15.350 x 15.350 x 1.500
Unit Dimensions (hwd / cm)	38.99 x 38.99 x 3.81
Unit Weight (lbs.)	2.260
Unit Weight (kg)	1.03
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.