

Cable Runway Radius Drop for 18 in. Straight & 90-Degree Ladder Sections - Hardware Included

MODEL NUMBER: SRLRADIUS18



Maintains a proper cable bend radius for cables that are routed down from your ladder system and retains their integrity.

Features

Ensures a Proper Bend Radius to Reduce Cable Stress and Keep Your Ladder System NeatThe SmartRack® SRLRADIUS18 helps reduce bend-induced stress, pinching, pressure points and fatigue in your cable ladder system. It mounts to the cross member of an 18-inch-wide ladder section to route stubborn cables down from the runway. This allows for builds that are more comprehensive and keeps everything neat atop the ladder system. All mounting and installation hardware is included. The cable radius drop fits solid and tubular steel runway measuring 1.5 x 0.375 inches (38 x 9.5 millimeters). The SRLRADIUS18 is designed for SRCABLELADDER18, SRL90BEND18 and other compatible 18-inch straight and 90-degree ladder sections.

Highlights

- 3 integrated posts and toolless installation for easy, reliable cable management
- Compatible with 18 in. straight and 90-degree-bend ladder sections
- Fits solid and tubular steel runway measuring 1.5 x 0.375 in. (38 x 9.5 mm)
- Includes necessary mounting and installation hardware for immediate use

Applications

- Organize a ladder runway system outside your data center's rack enclosure or open frame rack
- Keep cables affixed in the fixed posts without tying them to other cables
- Reduce stress, pinching, pressure points and fatigue in your cable ladder system

System Requirements

- Compatible with 18 in. straight and 90-degree-bend ladder sections, including SRCABLELADDER18 and SRL90BEND18

Package Includes

- Radius drop
- (3) Cable spools
- (3) Screws
- (3) M5 lock nuts
- (2) Clevis pins
- (2) Cotter pins
- Installation guide

Specifications

OVERVIEW	
UPC Code	037332214546
Accessory Type	Cable Management Accessories
PHYSICAL	
Color	Black



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Dimensions (hwd / in.)	5.12 x 19.09 x 7.28
Shipping Dimensions (hwd / cm)	13.00 x 48.49 x 18.49
Shipping Weight (lbs.)	2.86
Shipping Weight (kg)	1.30
Unit Dimensions (hwd / in.)	3.050 x 16.850 x 5.120
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.