

30W USB-C Wall & Travel Charger with Apple Watch Pad - MFi Certified, Compact 1-Port Design - White

MODEL NUMBER: U280MS-2N1-WH2



Travel charger with PD charging powers your smartphone, tablet or Apple Watch in a hotel or airport.

Features

Stay Powered Anywhere with USB-C and Apple Watch Charging Support

The U280MS-2N1-WH2 is the perfect all-in-one solution for keeping your essential devices powered at home, in the office, or on the go. Whether you're in a hotel, airport, coffee shop, or library, this travel-ready charger eliminates cable clutter with a direct plug-in design and folding prongs. Certified by Apple (MFi), this dual-purpose charger supports a wide range of mobile devices. The USB-C Power Delivery (PD) port delivers up to 30W, ideal for fast charging your iPhone, iPad, Android phone, tablet, or handheld gaming console (Device-specific charging cable sold separately). **Note:** This charger is designed for devices that require 30W or less. Charging laptops or high-power devices may result in reduced performance or overheating.

MagSafe-Compatible Charging for Apple Watch

The integrated MagSafe-compatible magnetic charging pad securely holds your Apple Watch in place while delivering up to 3W of wireless power. Built-in magnets align your watch perfectly every time, ensuring a stable and reliable charge—no slipping or disconnecting.

Built-In Safety and Travel-Ready Design

Equipped with overcurrent, overload, overvoltage, and short circuit protection, this charger keeps your devices safe while powering up. Its compact size and foldable NEMA 1-15P plug make it easy to pack and perfect for travel.

Specifications

OVERVIEW	
UPC Code	037332288189
Charging Form Factor	Direct Plug-In
Product Type	USB Charger; Wall Charger; Wireless Charger
Device Compatibility	Amazon Kindle; Phone; Tablet; Video Game System; Watch
Technology	USB

Highlights

- Cord-free convenience—plugs directly into the wall for easy setup and a clutter-free charging space
- Fast USB-C charging delivers up to 30W with PD and PPS support for rapid charging of phones, tablets, and more
- Apple Watch Ready—built-in MagSafe-compatible pad charges your Apple Watch wirelessly at up to 3W
- Built-in safety features protect your devices with overcurrent, overload, overvoltage, and short circuit protection
- Travel-friendly design is compact and lightweight, with folding prongs for easy packing and portability

System Requirements

- Works with all MagSafe-compatible smartwatches, including Apple Watch
- USB-C port is intended for use with smartphones and tablets, including iPhones and iPads

Package Includes

- U280MS-2N1-WH2 30W USB Wall/Travel Charger
- Quick Start Guide



Powering Business Worldwide

TRIPP LITE
SERIES

Country/Region	North America
Host Connector	USB C (FEMALE)
INPUT	
Nominal Input Voltage(s) Supported	100V AC; 110V AC; 115V AC; 120V AC; 127V AC; 12V DC; 140V AC; 200V AC; 208V AC; 220V AC; 230V AC; 240V AC
Maximum Input Amps	1
Input Connection Type	NEMA 1-15P
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
Input Frequency	50/60 Hz
Input Plug Type	NEMA 1-15P
Input Current	100-240V, 0.85A (Max)
Bus Powered	No
Power Source	AC Adapter; USB
OUTPUT	
Output Capacity (Watts)	30
Continuous Output Capacity (Watts)	30
Overload Protection	Yes
POWER	
Power Source Type	AC Adapter
Power Source	Unit (Included)
Power Consumption (Watts)	30.00
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	30W
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	(1) NEMA 1-15P (NON-POLARIZED)
Side B - Connector 1	USB C (FEMALE)
Side B - Connector 2	WIRELESS CHARGING COIL
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	N/A
CHARGING	
Number of Charging Ports	2



Powering Business Worldwide

TRIPP LITE
SERIES

Total Charging Amps	3
Total Charging Watts	30
Charging Method	Magnetic Charger; USB; Wireless
Charging Method Detail	(x1) Wireless magnetic charging strip supports up to 3 Watts of charging power for magnetic charging-enabled devices(x1) USB-C port supports up to 30 Watts of charging power for USB-enabled devices
Charging Port Type	(1) USB C (FEMALE); (1) WIRELESS CHARGING COIL
Charging Ports Details	(x1) USB-C female charging port provides up to 30W PD Charging or PPS Charging to Apple, Samsung or other smartphones and tablets in the following outputs: PD Charging: 5V/3A (15W), 9V/3A (27W), 12V/2.5A (30W), 15V/2A (30W), 20V/1.5A (30W)PPS Charging: 5-11V/3A (30W Max)(x1) MagSafe charging pad provides up to 3W to Apple Watch or other compatible smart watches
Magnetic Charging	Yes
Wireless Charging	Yes
Overcharge Protection	Yes
Compatible Devices	Smartphone; Tablet; Video Game Console
PHYSICAL	
Color	White
Material of Construction	PC (PLASTIC), PC945 UL94V-0
Cable Jacket Color	White
Connector Color	White
Charging Station Form Factor	Direct Plug-In
Total Number of Ports	2
Unit Dimensions (hwd / in.)	2.130 x 1.540 x 1.610
Unit Dimensions (hwd / cm)	4.17 x 5.4 x 3.9
Unit Dimensions (hwd / mm)	41.7 x 54 x 39
Unit Packaging Type	Box
Unit Weight (lbs.)	0.11
Unit Weight (kg)	0.05
ENVIRONMENTAL	
Operating Temperature Range	32° to 77°F (0° to 25°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% to 90% RH (NON-CONDENSING)
Storage Humidity Range	5% to 95% RH (NON-CONDENSING)
FEATURES & SPECIFICATIONS	
GaN Technology	No
Overcurrent Protection	Yes
Overvoltage Protection	Yes



Powering Business Worldwide

TRIPP LITE
SERIES

Over Current Protection	Yes
Driver Required	No
Qi Compliant	Yes
Over Temperature Protection	Yes
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 62368-1 (Canada); UL 62368-1
Product Compliance	FCC (USA); FCC Part 15 Class B (USA); WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.