

#### Important Note

The P311-006 is a 3-pole 3.5mm Mini Stereo Audio extension cable, designed for use with speakers and headphones that provide audio only. For headsets that support both speaker and microphone functionality, the 4-pole P318-006-MF 3.5mm Mini Stereo Audio extension cable is recommended.

## 3.5mm Mini Stereo Audio Extension Cable for Speakers and Headphones (M/F), 6 ft. (1.83 m)

MODEL NUMBER: **P311-006**



Extends the distance between 3.5mm stereo connections.

#### Features

- 6-ft. 3.5mm Male to 3.5mm Female Extension Cable
- Fully molded ends
- Braided shielding
- Nickel-plated connectors

## Specifications

| OVERVIEW                       |                |
|--------------------------------|----------------|
| UPC Code                       | 037332174130   |
| Technology                     | Stereo Audio   |
| Cable Type                     | Passive        |
| CONNECTIONS                    |                |
| Side A - Connector 1           | 3.5MM (MALE)   |
| Side B - Connector 1           | 3.5MM (FEMALE) |
| Latching or Gripping Connector | No             |

#### Highlights

- 6-ft. 3.5mm Male to 3.5mm Female
- Fully shielded

#### Package Includes

- 6-ft. 3.5mm M/F Mini-Stereo Audio Extension Cable



Powering Business Worldwide

TRIPP LITE  
SERIES

| PHYSICAL                            |                           |
|-------------------------------------|---------------------------|
| Color                               | Black                     |
| Cable Jacket Color                  | Black                     |
| Cable Length (ft.)                  | 6                         |
| Cable Length (m)                    | 1.83                      |
| Shipping Dimensions (hwd / in.)     | 9.00 x 7.00 x 0.50        |
| Shipping Dimensions (hwd / cm)      | 22.86 x 17.78 x 1.27      |
| Shipping Weight (lbs.)              | 0.07                      |
| Shipping Weight (kg)                | 0.03                      |
| FEATURES & SPECIFICATIONS           |                           |
| IP68 Rated                          | No                        |
| IP20 Rated                          | No                        |
| STANDARDS & COMPLIANCE              |                           |
| Product Compliance                  | RoHS; REACH               |
| WARRANTY & SUPPORT                  |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.