

2U UPS Replacement 48VDC Battery Cartridge (1 Set of 4) for Select SmartPro UPS

MODEL NUMBER: **RBC94-2U**



Highlights

- certified premium battery cartridge
- Pre-assembled and wired battery kit offers simple installation
- Rugged leakproof construction
- Maintenance free
- Wide operating temperature range

Package Includes

- One pre-assembled battery pack consisting of four 12V batteries

Description

Premium UPS replacement battery cartridges breathe new life into UPS systems suffering from expired or weak internal batteries. Each replacement battery cartridge is carefully screened and certified to meet or exceed original specifications and ships ready for installation into your UPS system. Reusable packaging holds expired batteries for recycling center delivery. See UPS replacement battery web page to confirm compatibility and quantity required.

COMPATIBLE WITH SMART1500RML2U, SMART2200RML2U, SMART3000RM2U, SU1500RTL2Ua, SU2200RTL2Ua and other UPS systems referencing this RBC.

Features

- Restores UPS runtime performance to original specifications
- Comes pre-assembled and ready for installation
- Reusable packaging holds expired batteries for recycling center delivery

Specifications

OVERVIEW	
UPC Code	037332122308
BATTERY	
DC System Voltage (VDC)	48
Included Battery Set	Contains (4) 12V 9AH sealed lead acid batteries
Typical Battery Lifespan	3 to 5 years, depending on UPS operating conditions
PHYSICAL	
Rack Height	2U
Minimum Required Rack Depth (cm)	40.64



Powering Business Worldwide

TRIPP LITE
SERIES

Minimum Required Rack Depth (inches)	16
Shipping Dimensions (hwd / in.)	14.90 x 4.60 x 11.40
Shipping Dimensions (hwd / cm)	37.85 x 11.68 x 28.96
Shipping Weight (lbs.)	28.05
Shipping Weight (kg)	12.72
Unit Dimensions (hwd / in.)	2.750 x 8.500 x 12.250
Unit Dimensions (hwd / cm)	6.985 x 21.59 x 31.115
Unit Weight (lbs.)	26.2
Unit Weight (kg)	11.88
ENVIRONMENTAL	
Relative Humidity	0-95% non-condensing
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.