

SmartRack Exhaust Duct Kit for SRCOOL7KRM and SRCOOL7KRME

MODEL NUMBER: SRCOOL7KDUCT



Exhaust duct accessory for Tripp Lite SRCOOL7KRM and SRCOOL7KRME. Directs and disperses heat from the air conditioning unit through an upper vent into your facility's ventilation system.

Description

The SRCOOL7KDUCT SmartRack® Exhaust Duct Kit is a venting system accessory for the SRCOOL7KRM and SRCOOL7KRME Rack-Mounted Air Conditioning Units. It directs and disperses heat from the SRCOOL7KRM and SRCOOL7KRME through an upper vent into your facility's dropped ceiling plenum, return air duct or other standard ventilation system. By keeping your rack equipment cool and performing at its peak, the SRCOOL7KDUCT helps the SRCOOL7KRM and SRCOOL7KRME reduce your cooling and energy costs.

Ideal for small-space applications where heat is unlikely to disperse on its own, such as an IT closet, the SRCOOL7KDUCT installs using the included hardware. Two magnetic tube adapters attach to the rack's vented rear door to make the kit compatible with EIA-standard rack enclosures and open frame racks that accommodate the SRCOOL7KRM and SRCOOL7KRME.

Features

Reduces Your Cooling and Energy Costs

- Exhaust duct accessory for SRCOOL7KRM and SRCOOL7KRME
- Directs and disperses heat through your facility's ventilation system
- Ideal for small IT closets where heat is unlikely to disperse on its own
- Helps keep rack equipment cool and performing at its peak
- Installs using included hardware
- Compatible with EIA-standard rack enclosures and open frame racks that accommodate SRCOOL7KRM and SRCOOL7KRME

Specifications

OVERVIEW	
UPC Code	037332190697
Accessory Type	Duct Kit
Accessory Class	Rack Accessories

Highlights

- Helps the SRCOOL7KRM and SRCOOL7KRME reduce cooling and energy costs
- Ideal for small spaces, such as IT closets
- Compatible with most EIA-standard racks and rack enclosures
- Installs using included hardware
- Keeps rack equipment performing at its peak

Package Includes

- Manifold assembly
- Short exhaust tube
- Long exhaust tube (D 5.7" x L 3m)
- (2) Magnetic tube adapters
- Ceiling adapter
- Ceiling tile insert
- (4) M4 x 12 mm screws
- (4) Self-tapping screws
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

COOLING	
Cooling Type	Passive
PHYSICAL	
Housing Color	Black
Shipping Dimensions (hwd / in.)	14.76 x 12.40 x 24.80
Shipping Dimensions (hwd / cm)	37.49 x 31.50 x 62.99
Shipping Weight (lbs.)	13.33
Shipping Weight (kg)	6.05
Unit Dimensions (hwd / in.)	11.400 x 17.100 x 4.800
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.