

SmartRack 3U Fan Panel - 3-120V high-performance fans; 210 CFM; 5-15P plug

MODEL NUMBER: SRFAN3U

Highlights

- 3U Panel-mount Triple Fan Accessory



Description

This SRFAN3U SmartRack® panel-mount Triple Fan Accessory (for use with SmartRacks) is ideal for increasing the ventilation of SmartRacks, enclosures and server cabinets. The unit features three four-inch 120V fans mounted in a 3U panel, six-foot (1.8-meter) cord and mounting hardware.

Features

- SRFAN3U SmartRack Panel-mount Triple Fan Accessory (for use with SmartRacks) is ideal for increasing the ventilation of SmartRacks, enclosures and server cabinets
- The unit features (3) 4-in.-120V fans mounted in a 3U panel, 6-ft. (1.83 m) cord
- Includes mounting hardware

Specifications

OVERVIEW	
UPC Code	037332144836
Accessory Type	Cooling Accessories; Fan Panel
Accessory Class	Cooling Accessories
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Nominal Input Voltage Description	120V AC 50/60 Hz
Input Connection Type	NEMA 5-15P
Input Plug Features	NEMA 5-15P
Voltage Compatibility (VAC)	120
Input Frequency	50/60 Hz



Powering Business Worldwide

TRIPP LITE
SERIES

Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
OUTPUT	
Frequency Compatibility	50 / 60 Hz
COOLING	
Cooling Type	Passive
PHYSICAL	
Rack Height	3U
Shipping Dimensions (hwd / in.)	6.00 x 3.00 x 20.00
Shipping Dimensions (hwd / cm)	15.24 x 7.62 x 50.80
Shipping Weight (lbs.)	7.55
Shipping Weight (kg)	3.42
Unit Dimensions (hwd / in.)	5.220 x 18.870 x 2.070
Unit Dimensions (hwd / cm)	13.26 x 47.9 x 5.26
Unit Weight (lbs.)	5.5
Unit Weight (kg)	2.49
FEATURES & SPECIFICATIONS	
Sound Level (Noise)	45dB
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.