


# Toolless Horizontal 4-Way Junction for Fiber Routing System, 120 mm (5 in.)

MODEL NUMBER: SRFC5JUNT4



120 mm junction section creates a 4-way cross intersection with 90-degree angles in your fiber management system.

## Features

### High-Impact PVC 4-Way Junction Helps You Create Fiber Cable Routing Intersections

The SmartRack® SRFC5JUNT4 connects to four channel sections or other fittings in your fiber routing system to create a horizontal four-way cross intersection with two exits. Four of SRFC5CPL5 couplers (sold separately) are required to complete your installation. Made from durable, lightweight PVC material, this 4-way junction connects using the couplers' included hardware to help keep your fiber optic cable bundles neat and organized. Screws tighten by hand with no tools required to complete a professional, finished look in your data center, network closet or industrial space.

## Highlights

- Allows you flexibility in creating your custom fiber optic cable routing system
- Constructed from durable but lightweight PVC plastic
- Easy to install with your fiber routing system with no tools needed
- Requires 4 SRFC5CPL5 couplers (sold separately)

## Applications

- Create a fiber routing system along the wall or ceiling of your data center or network closet or across the tops of the rack enclosures

## System Requirements

- 4 x SRFC5CPL5 couplers (sold separately)

## Package Includes

- Horizontal 4-way junction, 120 mm
- Installation guide

# Specifications

| OVERVIEW                               |                              |
|----------------------------------------|------------------------------|
| UPC Code                               | 037332240965                 |
| Product Type                           | Junction                     |
| Accessory Type                         | Cable Management Accessories |
| Cable Management System Component Type | Junction                     |
| PHYSICAL                               |                              |
| Color                                  | Yellow                       |
| Shipping Dimensions (hwd / in.)        | 5.11 x 14.56 x 14.56         |
| Shipping Weight (kg)                   | 1.25                         |
| Unit Dimensions (hwd / in.)            | 4.645 x 13.858 x 13.858      |
| Unit Dimensions (hwd / cm)             | 11.8 x 35.2 x 35.2           |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                     |                         |
|-------------------------------------|-------------------------|
| Unit Weight (lbs.)                  | 1.748                   |
| Unit Weight (kg)                    | 0.79                    |
| STANDARDS & COMPLIANCE              |                         |
| Product Compliance                  | RoHS; EIA/ECA-310-E     |
| WARRANTY & SUPPORT                  |                         |
| Product Warranty Period (Worldwide) | 5-year limited warranty |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.