


Triangular Wall Support Kit for 12 & 18 in. Cable Runway, Straight & 90-Degree - Hardware Included

MODEL NUMBER: SRLTRISUPPORT



Easy-to-install triangular aluminum bracket safely and securely mounts to a wall surface to support cable runway.

Features

Cable Ladder Triangular Support Bracket Secures Your Data Center's Runway System to a Wall This innovative SmartRack cable runway wall support kit creates a secure connection between your server rack and the wall of your server room or data center. Mounting and installation hardware is included, except for appropriate fasteners to secure the durable aluminum wall bracket. The mounting surface must be able to support the combined equipment load safely. Be sure to use suitable mounting means when installing to cinder block, concrete, drywall or wooden studs. The SRLTRISUPPORT is constructed of 0.25 x 2 inches (6 x 51 millimeters) aluminum and supports up to 100 pounds (45 kilograms). It is designed for SRCABLELADDER, SRCABLELADDER18, SRL90BEND12, SRL90BEND18 and other compatible straight and 90-degree ladder sections.

Highlights

- For safely routing runway from the wall to outside an enclosure or open frame rack
- 0.25 x 2 in. aluminum wall bracket supports runway and cabling up to 100 lb. (45.4 kg)
- Compatible with 12 in. and 18 in. straight and 90-degree-bend ladder sections
- Works with all SmartRack® ladder system accessories and runways
- Includes all necessary mounting and installation hardware for immediate use

Applications

- Secure a ladder runway system from a rack enclosure or open frame rack to the wall of your data center or server room

System Requirements

- Compatible with straight and 90-degree-bend ladder sections, including SRCABLELADDER, SRCABLELADDER18, SRL90BEND12 and SRL90BEND18

Package Includes

- Wall bracket
- (2) M8 J-bolts
- (2) M8 lock washers
- (2) M8 hex nuts
- Installation guide

Specifications

OVERVIEW	
UPC Code	037332214485
Accessory Type	Cable Management Accessories
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Shipping Dimensions (hwd / in.)	23.28 x 23.62 x 3.34
Shipping Dimensions (hwd / cm)	59.13 x 60.00 x 8.50



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Weight (lbs.)	4.54
Shipping Weight (kg)	2.06
Unit Dimensions (hwd / in.)	23.280 x 23.622 x 3.346
Unit Dimensions (hwd / cm)	59.13 x 60.00 x 8.50
Unit Weight (lbs.)	3.100
Unit Weight (kg)	1.41
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.