




*Quality Products. Service Excellence.*

## Type 4X Sloped Top Stainless Steel Freestanding 2STFS Series



### Application

- Designed to enclose electrical and/or electronic equipment and protect against harsh, industrial environments for larger applications.
- 20° sloped top prevents water from resting on top of enclosure.

### Standards

- UL 508A Type 3R, 12, 4, 4X
- CSA Type 3R, 12, 4, 4X
- Complies with
  - NEMA Type 3R, 12, 13, 4, 4X
  - IEC 60529, IP66
- Appropriate components are required to maintain these standards.

### Construction

- Formed from 12 gauge 304 or 316L stainless steel with smooth, continuously welded seams.
- Flange trough collar (FTC) around door opening excludes liquids and contaminants.
- Heavy duty lifting eyes are anchored into reinforced top corners.
- Removable doors are secured with bullet style, heavy duty, lift off hinges.
- Formed 10 gauge steel inner panel is provided on collar studs.
- Panel supports are provided.
- Center post is removable, providing easy panel installation.
- Heavy duty three point latching mechanism with heavy duty roller ends is provided for ease of door closing.
- Seamless poured-in place gasket.
- Stainless steel door handles complete with padlock hasp.
- A provision for mounting fluorescent lighting is provided.
- A bonding stud is provided in the door and a grounding stud is provided in the enclosure for each door.
- A literature pocket is provided for the inside of the door.

### Finish

- Door and enclosure are natural stainless steel with a smooth, brushed finish..
- Inner panel is finished in white powder coating.

### Accessories

- |                             |                       |
|-----------------------------|-----------------------|
| • Wash Down Floor Stand Kit | • Door Stop Kit       |
| • Window Kits               | • Climate Control     |
| • Lighting                  | • General Accessories |

**New and improved PDF part  
drawing files with more detail  
now available.**

Click part number in table below  
to access PDF, DXF, and STEP files.

| 304 S.S.      | 316 S.S.       | Enclosure |       |       |       | Panel |       |
|---------------|----------------|-----------|-------|-------|-------|-------|-------|
| Part Number   | Part Number    | H1        | H2    | W     | D     | H     | W     |
| 2STFS747512SS | 2STFS747512S16 | 74.13     | 79.49 | 75.13 | 12.13 | 68.00 | 68.00 |
| 2STFS747518SS | 2STFS747518S16 | 74.13     | 79.49 | 75.13 | 18.13 | 68.00 | 68.00 |
| 2STFS747524SS | 2STFS747524S16 | 74.13     | 79.49 | 75.13 | 24.13 | 68.00 | 68.00 |

Tags: freestanding, stainless steel, 304, 316, Type 4X, sloped top, large

Data subject to change without notice

© 2025. Hammond Manufacturing Ltd. All rights reserved.