

Center-Hinged Wall-Mount Rack (220 lb) *HWMR Series*

Center-hinged wall rack for mounting 19" equipment with stable access for servicing and cable management.

MOST POPULAR



Key Features and Benefits

- Steel construction (220 lb **capacity**) provides reliable support for switches, patch panels, and rack-mounted equipment.
- Center-hinged wall-mount rack design (19" rack compatible) provides split access from the middle for installation, servicing, and cable management.
- Center hinge design allows equipment to open from the middle without shifting load off the wall improves stability during servicing.
- One (1) pair of 10-32 threaded mounting rails supports standard rack equipment and consistent installation. Includes starter hardware pack with **SCREW1032-50** screws for equipment mounting.
- Multiple cable entry knockouts and mounting points support organized cable routing in wall-mounted installations.
- TAA-compliant, manufactured in North America supports government procurement requirements and ensures consistent quality.
- Black powder coat finish (GREENGUARD Gold, TSCA, RoHS compliant) supports indoor air quality and environmental compliance.

The HWMR Series center-hinged wall mount rack provides a durable solution for mounting 19-inch rack equipment in telecom and IT environments. Its center-hinged design allows stable access from the middle, simplifying installation, servicing, and cable management without requiring a full cabinet enclosure.

Designed for structured cabling and network deployments, the HWMR supports open-frame mounting with a 220 lb load capacity and organized cable routing. It is ideal for applications requiring frequent maintenance and reliable wall-mounted support.

When another product may be a better choice

- When you need a fixed wall rack with no hinged access, consider our **RB-2PW** Series.
- When you need an adjustable depth wall bracket, consider our **APB** Series.
- When you need a wall bracket with an integrated shelf, consider our **APBS** Series.
- When you need a fully enclosed cabinet with security, consider our **HWM** or **HWC** Series.



This product is not designed nor intended to be used for non-wall mounted applications.

Gallery



Accessories

- Vertical Cable Manager for Wall Mount Racks
- Rack Panels for Rack Optimization
- Universal Rack Shelf Fixed Steel (Up to 200 lb Capacity)
- Rack Mount Keyboard & Equipment Shelf
- Adjustable Rack Mount DIN Rail Kit 2U Steel DIN Rail Panel
- Rack Unit Label Kit Adhesive Rack Rail Numbering Labels
- We Manufacture PDUs and Outlet Strips
- Rack Cable Tie Down Bracket Steel Cable Anchor
- Rack Cable Management Ring
- Clamping Rack Shelf
- Adjustable Rack Shelf
- Hinged Window Rack Security Cover
- Hardware for Rack Mounting Solutions



Part No.	Height	Overall Dimensions			Rack Units	Mounting (Usable Center Swing) Dimensions				Vertical Cable Manager
		Width	Min Depth	Max Depth		Height	Width	Min Depth	Max Depth	Part No.
HWMR1912UBK	26.50	20.00	18.00	24.00	12U	21.00	19.00	15.10	21.10	WRCM12U4BK
HWMR1920UBK	40.50	20.00	18.00	24.00	20U	35.00	19.00	15.10	21.10	WRCM20U4BK
HWMR1924UBK	47.50	20.00	18.00	24.00	24U	42.00	19.00	15.10	21.10	WRCM24U4BK
HWMR1932UBK	61.50	20.00	18.00	24.00	32U	56.00	19.00	15.10	21.10	WRCM32U4BK

Note: Mounting Dimensions / Usable Depth is the maximum equipment depth that will allow the center section to swing unimpeded.

What's Inside the Box

Qty Included	Description	Replacement Part No.
1	Rack Frame	
2	Top and Bottom Cover	
2	Left Main Support Brackets	
2	Right Main Support Brackets	
2	Wall Mounting Vertical Supports	
1	Assembly Instructions	
1	Assembly Hardware Kit	
50	10-32 x 0.75in Rack Mounting Screws	SCREW1032-50

Where the HWMR series works best

- Telecom backboards and network demarcation points.
- Network closets requiring rear access without a full cabinet.
- Installations requiring stable access for servicing and cable management.
- Structured cabling environments with frequent maintenance needs.
- Wall-mounted installations where equipment must remain secure during servicing.

Applications and when to use the HWMR series

- Installations requiring center-hinged access for cable management and servicing.
- Applications needing open frame mounting with stable access during maintenance.
- Environments where equipment must be accessed frequently without removal.
- Deployments requiring balanced access from both sides of the rack.
- Installations where open mounting is preferred over enclosed cabinets.

Tags: **Swivel rack, swing gate rack, hinged rack, 2-post wall-mount rack, swinging 2-post rack, rotating equipment frame, swing frame, hinged swing gate, pivoting wall rack, center-hinged rack, wall-mount swing frame, telecom wall rack** *Data subject to change without notice.*