



Quality Products. Service Excellence.

2-Post Open Frame Rack RRTT Series

Load rated to 350 lbs (159 kg)



Features

- Constructed in 14-gauge steel.
- EIA compliant 19 inch mounting rails with punched round holes for use with clip nuts.
- Includes starter pack of **CLPKIT1032-25** screws and clip nuts.
- Includes large base for freestanding support of equipment.
- Finished in textured black powder paint. Complies with the Greenguard guidelines for indoor air quality.
- Self-squaring design ships un-assembled (some assembly required).
- 350 lbs (159 kg) **static load rating**.
- TAA-compliant for federal GSA schedule purchases within the USA.
- RoHS Compliant.
- Manufactured in North America within an ISO 9001:2015 certified facility.



 **Rack Mounting Hardware Included**



Accessories

- Cable Managers
- Hinged Clear Security Cover
- Adjustable Rack Shelf
- Deep Channel Rack Shelf
- Keyboard & Equipment Rack Shelf
- Adjustable Rack Mount DIN Rail Kit
- 10-32 Mounting Hardware
- We Manufacture PDUs and Outlet Strips
- Rack Panels
- Universal Rack Shelf
- Variable-Depth Rack Shelf
- Centered Rack Shelf
- Clamping Rack Shelf
- Rack Unit Label
- Bonding and Grounding

Part No.	Overall Dimensions			Rack Units	Mounting Dimensions	
	Height	Width	Base Depth		Height	Width
RRTT1921BK1	24.00	20.38	12.00	12U	21.00	19.00
RRTT1928BK1	31.00	20.38	12.00	16U	28.00	19.00

Turn your RRTT into an Adjustable Depth 4-Post Rack

Order Two (2) of following:	Order One (1) or Two (2) of the following:	Rack Units	Min Depth	Max Depth
RRTT Rack	Adjustable Depth Rack Shelf	Adjustable Depth Angle Brackets	Units	Depth
RRTT1921BK1	ADSU1825BK	-	12U	18.00 25.00
RRTT1921BK1	ADSU2536BK	RAAB2436BK	12U	25.00 36.00

Order Two (2) of following:	Order One (1) or Two (2) of the following:	Rack	Min	Max	
RRTT Rack	Adjustable Depth Rack Shelf	Adjustable Depth Angle Brackets	Units	Depth	Depth
RRTT1921BK1	ADSU3642BK	RAAB3648BK	12U	36.00	42.00
RRTT1928BK1	ADSU1825BK	-	16U	18.00	25.00
RRTT1928BK1	ADSU2536BK	RAAB2436BK	16U	25.00	36.00
RRTT1928BK1	ADSU3642BK	RAAB3648BK	16U	36.00	42.00

Tags: **Relay Rack, H-Frame, Homelab, Server Rack, Equipment Rack, Network Rack, Skeleton Rack, Telco Rack, Two-Post Rack, knock-down, knock down** *Data subject to change without notice*

© 2025. Hammond Manufacturing Ltd. All rights reserved.