

## Adapter, Metric to PG Thread, Nickel-Plated Brass

### Material:

- Nickel-plated brass
- O-ring: Nitril

### Characteristics:

- Metric external thread
- PG internal thread
- Hexagon

| External thread | Internal thread | SW mm | Thread length mm | Complete length mm | Cat. No. without O-ring | Cat. No. with O-ring | Std. Pk. |
|-----------------|-----------------|-------|------------------|--------------------|-------------------------|----------------------|----------|
| <b>Form A</b>   |                 |       |                  |                    |                         |                      |          |
| <b>Metric</b>   | <b>PG</b>       |       |                  |                    |                         |                      |          |
| M 12 x 1.5      | PG 7            | 14    | 7                | 17                 | 6604712                 | 6604658              | 100      |
| M 16 x 1.5      | PG 9            | 18    | 7                | 17.5               | 6604716                 | 6604660              | 50       |
| M 16 x 1.5      | PG 11           | 20    | 7                | 18                 | 6604715                 | 6604661              | 50       |
| M 16 x 1.5      | PG 13.5         | 22    | 7                | 19.5               | 6604709                 | 6604662              | 50       |
| M 16 x 1.5      | PG 16           | 24    | 7                | 21.5               | 6604717                 | 6604663              | 50       |
| M 20 x 1.5      | PG 11           | 22    | 7                | 18                 | 6604720                 | 6604666              | 50       |
| M 20 x 1.5      | PG 13.5         | 22    | 7                | 19.5               | 6604721                 | 6604664              | 50       |
| M 20 x 1.5      | PG 16           | 24    | 7                | 20.5               | 6604722                 | 6604667              | 50       |
| M 20 x 1.5      | PG 21           | 32    | 7                | 22.5               | 6604708                 | 6604668              | 50       |
| M 25 x 1.5      | PG 16           | 27    | 8                | 21.5               | 6604726                 | 6604669              | 50       |
| M 25 x 1.5      | PG 21           | 32    | 8                | 23.0               | 6604725                 | 6604670              | 50       |
| M 25 x 1.5      | PG 29           | 40    | 8                | 25                 | 6604727                 | 6604676              | 20       |
| M 32 x 1.5      | PG 21           | 34    | 8.5              | 23.5               | 6604729                 | 6604672              | 20       |
| M 32 x 1.5      | PG 29           | 40    | 8.5              | 25.0               | 6604732                 | 6604681              | 10       |
| M 40 x 1.5      | PG 29           | 42    | 8.5              | 25                 | 6604734                 | 6604675              | 10       |
| M 40 x 1.5      | PG 36           | 50    | 8.5              | 28.0               | 6604740                 | 6604685              | 10       |
| M 50 x 1.5      | PG 36           | 52    | 9.5              | 29                 | 6604742                 | 6604678              | 10       |
| M 50 x 1.5      | PG 42           | 58    | 9.5              | 31.5               | 6604750                 | 6604689              | 5        |
| M 63 x 1.5      | PG 42           | 65    | 10.5             | 32.5               | 6604752                 | 6604692              | 1        |
| M 63 x 1.5      | PG 48           | 65    | 10.5             | 32.5               | 6604763                 | 6604694              | 1        |
| M 75 x 1.5      | PG 48           | 80    | 11.5             | 34.5               | 6604764                 | 6604695              | 1        |
| <b>Form B</b>   |                 |       |                  |                    |                         |                      |          |
| M 16 x 1.5      | PG 7            | 18    | 7                | 10.5               | 6604713                 | 6604659              | 100      |
| M 20 x 1.5      | PG 9            | 22    | 7                | 11                 | 6604719                 | 6604665              | 50       |
| M 25 x 1.5      | PG 9            | 27    | 8                | 12                 | 6604707                 | 6604674              | 50       |
| M 25 x 1.5      | PG 11           | 27    | 8                | 12                 | 6604723                 | 6604671              | 50       |
| M 25 x 1.5      | PG 13.5         | 27    | 8                | 12                 | 6604724                 | 6604673              | 50       |
| M 32 x 1.5      | PG 13.5         | 34    | 8.5              | 12.5               | 6604706                 | 6604677              | 20       |
| M 32 x 1.5      | PG 16           | 34    | 8.5              | 12.5               | 6604728                 | 6604679              | 20       |
| M 32 x 1.5      | PG 21           | 34    | 8.5              | 12.5               | 6604730                 | 6604680              | 20       |
| M 40 x 1.5      | PG 16           | 42    | 8.5              | 13.5               | 6604705                 | 6604682              | 10       |
| M 40 x 1.5      | PG 21           | 42    | 8.5              | 13.5               | 6604733                 | 6604683              | 10       |
| M 40 x 1.5      | PG 29           | 42    | 8.5              | 13.5               | 6604735                 | 6604684              | 20       |
| M 50 x 1.5      | PG 21           | 52    | 9.5              | 15.5               | 6604704                 | 6604686              | 10       |
| M 50 x 1.5      | PG 29           | 52    | 9.5              | 15.5               | 6604741                 | 6604687              | 10       |
| M 50 x 1.5      | PG 36           | 52    | 9.5              | 15.5               | 6604743                 | 6604688              | 10       |
| M 63 x 1.5      | PG 29           | 65    | 10.5             | 17.5               | 6604703                 | 6604690              | 5        |
| M 63 x 1.5      | PG 36           | 65    | 10.5             | 17.5               | 6604751                 | 6604691              | 5        |
| M 63 x 1.5      | PG 42           | 65    | 10.5             | 17.5               | 6604753                 | 6604693              | 5        |



Form A



Form B