



Quality Products. Service Excellence.

Type 4, 4X Mild Steel and Stainless Steel Turret Units Series 2000

Modular Console System



Application

- Ideal as a housing for video screens.
- Flexible design provides panel mount or rack mount capabilities for a variety of applications.
- Generally used in combination with other modular console components (ie. base, pedestal, and/or desk).
- Available in either Standard (supported by Base, Pedestal, or Standard Desk) or Deep (supported by Deep Desk only) format.
- Smooth lines and clean edges provide an attractive, contemporary appearance.

Standards



- UL 508A Type 3R, 4,12 (Stainless Steel, add 4X)
- CSA Type 3R, 4, 12, 13 (Stainless Steel, add 4X)
- EIA RS-310-E
- Complies with
 - NEMA Type 3R, 4, 12 (Stainless Steel, add 4X)
 - IEC 60529, IP66



Construction

- Formed 14 gauge steel bodies with 14 gauge steel doors. Also offered with formed 14 gauge 304 stainless steel bodies with 14 gauge 304 stainless steel doors.
- Smooth, continuously welded seams without knockouts or holes.
- Body stiffeners are provided where required for increased strength and rigidity.
- Offered in 4 widths 24", 36", 48" and 60".
- Features solid sides and top, solid door on front (opens down) and back (opens up), and open bottom.
- Front door features sliding rod mechanism, which allows a 102° opening when in the lowered position.
- Rear door features manual, 3 position adjustable door stop which provides convenient support while door in open position.
- Formed lip on enclosure excludes flowing liquids and contaminants.
- Slotted quarter turn oil-tight latches secure the door, with optional tamper resistant and locking latches available.
- Stainless steel models utilize stainless steel hardware.
- Oil resistant gaskets are permanently secured.
- Features several internal stud locations for mounting of various accessories.
- A bonding screw is provided on the door and a grounding stud is provided in the enclosure.

Finish

- Available in RAL 7035 light gray textured powder coating and natural stainless steel with a smooth, brushed finish.
- 24" Front Window Door available in same finishes.

Accessories

- S2000 Internal Components
- S2000 External Components
- Quarter Turn Inserts and Keys
- Climate Control
- General Accessories
- S2000 Rack Components
- Quarter Turn Assemblies
- Padlock Adaptor
- Lighting

New and improved PDF part drawing files with more detail now available.

Click part number in table below to access PDF, DXF, and STEP files.

Standard Depth Turret

RAL 7035 Light	Stainless	Gray	Steel	Enclosure				
Part No.	Part No.			H	W	D1	D2	
2CLT202436	2CST202436	20.00	24.00	12.38	16.62			
2CLT203636	2CST203636	20.00	36.00	12.38	16.62			
2CLT204836	2CST204836	20.00	48.00	12.38	16.62			
2CLT206036	2CST206036	20.00	60.00	12.38	16.62			

Extra Deep Turret

RAL 7035 Light	Stainless	Gray	Steel	Enclosure				
Part No.	Part No.			H	W	D1	D2	
2CLT202443	2CST202443	20.00	24.00	16.62	23.31			
2CLT203643	2CST203643	20.00	36.00	16.62	23.31			
2CLT204843	2CST204843	20.00	48.00	16.62	23.31			
2CLT206043	2CST206043	20.00	60.00	16.62	23.31			

Tags: Series 2000, Type 4X, Type 4, stainless steel, turret, console, modular, screen, panel mount, rackmount, deep

Data subject to change without notice

© 2026. Hammond Manufacturing Ltd. All rights reserved.