

CONNECTOR 1

1. CONNECTOR 1 : 858-004-203RLS4, MOLDED STRAIGHT HOOD, COLOR BLACK
2. WIRE : 24AWG, 4 TWISTED PAIRS, UL2835, FOIL SHIELD, COLOR BLACK, 30V
3. CABLE DIAMETER : 6.50mm±0.19
4. PIN OUT :

WIRING SCHEMATIC

| | | |
|--------|---|--------------|
| Pin #1 | — | BLUE |
| Pin #2 | — | BLUE/WHITE |
| Pin #3 | — | ORANGE |
| Pin #4 | — | ORANGE/WHITE |
| SHELL | — | SHIELD |

CCA-000-MYYR214

| | | |
|----|---|-----------|
| 01 | = | 1 METER |
| 02 | = | 2 METERS |
| 03 | = | 3 METERS |
| 05 | = | 5 METERS |
| 10 | = | 10 METERS |

**SEE PAGE 3 FOR CABLE
SPECIFICATIONS

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OR SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.


DRAWN:
M. SIGMON
DATE:
04/21/2015

UNITS = "as indicated"

DO NOT SCALE FROM DRAWING

NorComp

| | | |
|----------------------------|-----------------------|----------|
| SCALE: NTS | SHEET 1 OF 3 | REV 5 |
| DWG NO. CCA-000-MYYR214 | | |



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OR SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
M. SIGMON
DATE:
04/21/2015

UNITS = mm


DO NOT SCALE FROM DRAWING

NorComp


| SCALE: | NTS | SHEET | OF | REV |
|---------|-----|-------|----|-----|
| DWG NO. | 2 | 3 | | 5 |

CCA-000-MYYR214

ELECTRICAL CHARACTERISTICS



| | |
|-----------------------|--|
| VOLTAGE RATING | : 30V |
| TEMPERATURE RATING | : 60°C |
| SPARK TEST | : AC-2000V/0.15 sec MIN. |
| DIELECTRIC STRENGTH | : AC-750V/1 sec MIN. |
| INSULATION RESISTANCE | : PE: DC-500V 15000 MΩHM/100M MIN. AT 20°C |
| CONDUCTOR RESISTANCE | : 24AWG - 93.2 ΩHM/KM MAX. AT 20°C |



COLOR CODE

1. BROWN * BROWN/WHITE
2. BLUE * BLUE/WHITE
3. ORANGE * ORANGE/WHITE
4. GREEN * GREEN/WHITE

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OR SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
M. SIGMON
DATE:
04/21/2015

DO NOT SCALE FROM DRAWING

NorComp

| | | | |
|----------------------------|------------|---------|----------|
| SCALE: NTS | SHEET 3 | OF 3 | REV 5 |
| DWG NO. CCA-000-MYYR214 | | | |