

10		9		8		7		6		5		4		3		2		1						
ITEM	MOLEX P/N	DESCRIPTION		QTY	UOM															FROM	TO	WIRE SIZE	WIRE TYPE	COLOR
A,B	503988000	2.5 W-W CRIMP PIN (CHAIN)		2	PC															A	B	28 AWG	UL 1007	BLACK




TABLE		
FG PART #	L	TITLE
2291141132	150±5	CP3.3 28AWG M-M 150 mm
2291141135	500±5	CP3.3 28AWG M-M 500 mm

NOTE:
1. CRIMPING TO BE DONE AS PER MOLEX STANDARDS.
2. THE PRODUCT SPECIFICATION RELIES ON THE TERMINALS & WIRE SPEC.

A	INITIAL RELEASE	ER	17-MAR-2025	NA	NA
REVISION	CHANGE NOTE	EC NO	DATE	CUSTOMER P/N	CUSTOMER REV

DETAIL		DESCRIPTION		DETAIL		DESCRIPTION	
		Continues Taping				PVC sleeve or Silicon sleeve	
		HST				T Dimension	
		Woven Braid				Convolutud Tube	
		Spot Taping				Customer Specific requirements	

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
= 0	DIMENSION UNITS	SCALE
= 0	mm	NTS
= 0	GENERAL TOLERANCES (UNLESS SPECIFIED)	
DIVISIONAL SYMBOLS	ANGULAR TOL	± °
	4 PLACES	±
	3 PLACES	±
	2 PLACES	±
	1 PLACE	±
	0 PLACES	±
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	THIRD ANGLE PROJECTION
		DRAWING
		A3-SIZE
		SERIES
		229114
		MATERIAL NUMBER
		SEE TABLE
		CUSTOMER
		GENERAL MARKET
		SHEET NUMBER
		1 OF 1

EC NO: 816292		2025/03/17	
DRWN: BHARAB5		2025/03/19	
CHK'D: NAVEEB6		2025/03/20	
APPR: RPAI01			
INITIAL REVISION:			
DRWN: BHARAB5		2025/03/17	
APPR: RPAI01		2025/03/20	

DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
2291141132		PSD	000	A

A3-SIZE		229114		SEE TABLE	GENERAL MARKET	1 OF 1
---------	--	--------	--	-----------	----------------	--------

DOCUMENT STATUS	P1	RELEASE DATE	2025/03/20	05:22:42
-----------------	----	--------------	------------	----------

9	8	7	6	5	4	3	2	1
---	---	---	---	---	---	---	---	---