



**Wiremold**  
**AF3 Series Raised Floor Box**  
Part No. AF3-YT



The AF3 Raised Floor and Stage Floor Box provides four separate compartments that accommodate up to eight gangs of communication, power and/or audio/ video devices. The top panel has a unique built-in service divider that accommodates a combination power, communication and audio/video devices. These dividers are arranged in a single-double, single-gang configuration. The lower panel provides single-gang activation points in a single service configuration. Die-cast aluminum housing provides added strength and reliability. Polycarbonate hinged lid and trim flange are available for carpet or tile applications, as well as a color choice of black, brown, or gray.

## Features & Benefits

The AF3 Raised Floor and Stage Floor Box provides four separate compartments that accommodate up to eight gangs of communication, power and/or audio/ video devices.

These dividers are arranged in a single-double, single-gang configuration. The lower panel provides single-gang activation points in a single service configuration.

The top panel has a unique built-in service divider that accommodates a combination power, communication and audio/video devices.

Die-cast aluminum housing provides added strength and reliability. Polycarbonate hinged lid and trim flange are available for carpet or tile applications, as well as a color choice of black, brown, or gray.

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786564519379
Country Of Origin	United States	Material	Die-Cast Aluminum
Construction	Assembled	Cover Material	Polycarbonate
Application Sector	Commercial	Standard	UL Listed Classified Raised Floor Box: File E2961 Guide QCIT, UL Listed Classified Raised Floor Box (prewired): File E51105 Guide QQVX, Meets Article 314 of NEC. Meets Article 12 2500 of CEC.
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Floor Box

### Dimensions

---

Product Weight US	6.808 lb	Cubic Capacity	305 in <sup>3</sup>
-------------------	----------	----------------	---------------------

---

Knockout Size	1/2 in, 3/4 in
---------------	----------------

---

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

---

### Trade Programs

---

USMCA	Yes
-------	-----

---

### Additional Information

---

RoHS Compliant	Yes
----------------	-----

---

### Technical Information

---

Floor Type	Carpet, Raised, Tile	Service Capacity	Triple
------------	----------------------	------------------	--------

---

Minimum Floor Depth	5 in	Box Capacity	8 Gangs
---------------------	------	--------------	---------

---

Cable Entry	Through Floor	Box Type	Recessed
-------------	---------------	----------	----------

---

Depth Behind Device Plates	2.75 in
----------------------------	---------

---